

# 16A 1M Connected Switch

## Device user guide

Information about features and functionality of the device.  
07/2024

# Legal Information

The information provided in this document contains general descriptions, technical characteristics and/or recommendations related to products/solutions.

This document is not intended as a substitute for a detailed study or operational and site-specific development or schematic plan. It is not to be used for determining suitability or reliability of the products/solutions for specific user applications. It is the duty of any such user to perform or have any professional expert of its choice (integrator, specifier or the like) perform the appropriate and comprehensive risk analysis, evaluation and testing of the products/solutions with respect to the relevant specific application or use thereof.

The Schneider Electric brand and any trademarks of Schneider Electric SE and its subsidiaries referred to in this document are the property of Schneider Electric SE or its subsidiaries. All other brands may be trademarks of their respective owner.

This document and its content are protected under applicable copyright laws and provided for informative use only. No part of this document may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Schneider Electric does not grant any right or license for commercial use of the document or its content, except for a non-exclusive and personal license to consult it on an "as is" basis.

Schneider Electric reserves the right to make changes or updates with respect to or in the content of this document or the format thereof, at any time without notice.

**To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any errors or omissions in the informational content of this document, as well as any non-intended use or misuse of the content thereof.**

---

# Table of Contents

Wiser App.....	5
Downloading the Wiser App .....	5
Creating an account.....	5
App settings .....	7
User .....	9
Adding a user .....	9
Removing a user.....	11
Location.....	11
Adding a new location .....	11
Removing a location.....	11
Energy.....	12
Flow.....	12
Insights .....	12
Notifications .....	13
Changing the password .....	13
Deleting an account.....	14
Customer support.....	14
Cybersecurity principles .....	14
Safety Information.....	16
16A 1M Connected Switch .....	17
For your safety .....	17
About this product.....	17
Installing the device .....	17
Pairing the device .....	18
Configuring the device .....	20
Renaming the device .....	20
Changing the device location .....	21
Adding devices to favourites .....	22
Removing devices from favourites.....	23
Creating a schedule .....	23
Automate .....	25
Voltage detection & load cut-off.....	25
Thermal cut-off value.....	26
Removing the device .....	27
Resetting the device .....	27
Changing the Wi-Fi access point.....	28
Changing the Wi-Fi access point while offline.....	29
Using the device.....	30
Switching On/Off the device manually.....	30
Switching On/Off the device using the app .....	30
Rooms .....	31
Notifications .....	33
History .....	34
Timeline .....	35
Quick (Action).....	36
Creating an automation for trigger .....	39
LED indication.....	42
Troubleshooting .....	43

---

Technical data .....	43
Trademarks.....	44

# Wiser App

Use the Wiser app to control Wiser devices and receive notifications.

## Downloading the Wiser App

Before you create an account, you need the Wiser app.

Download the Wiser app from the relevant app store:

### iOS

Requires iOS 13 or later

Search term: Wiser

<https://apps.apple.com/app/id6467395962>



### Andriod

Requires Android 8 or later

Search term: Wiser

<https://play.google.com/store/apps/details?id=com.schneiderelectric.soha>




## Creating an account


To control the devices from your smartphone, you need to create an account and log in.

To create an account:

1. On the welcome screen, tap **Register a New Account** (A).



2. Enter Username and Email.



3. Enter a password and re-enter in the password field.

**NOTE:** The password must meet at least the following criteria:

- Ten characters long
- Contain at least one lowercase letter
- Contain at least one uppercase letter
- Contain at least one number
- Contain at least one special character (!&^%\$#@().)

4. Read and tick the check box to agree with the **User Agreement** and **Privacy Notice**.

5. Tap **Register** (B).

The screenshot shows the 'Register' screen with a modal dialog for email verification. The dialog text reads: 'Verify your email', 'A verification email link has been sent to "XXXXXXXXXX@gmail.com".', 'Please click on the link to verify your account.', 'Click on Resend if you haven't received it.', and 'You have 5 attempts left'. There are two buttons in the dialog: 'Edit email' (labeled C) and 'Resend' (labeled D). The background form has fields for Username, Email, Password, and Re-enter Password, with a green 'Register' button at the bottom.

## 6. Activate account.

An e-mail will be sent to the specified e-mail address. Check your inbox and click the link in the e-mail.

**TIP:**

- If you do not see the email in your inbox, also check your spam folder.
- If you still have not received the email, tap **Resend** (D).
- You can update the information by tapping **Edit Email** (C) and request the email to be sent again.
- After confirming the e-mail, the Wiser app shows the confirmation that the setup is complete.

**NOTE:** You have a total of 5 attempts to send an email.

## 7. Enter your home address.

The screenshot shows the 'Add location' screen. It has a text input field with the placeholder 'Add new location'. Below the field is a green button labeled 'Next' (labeled E). The screen also includes a back arrow and a title 'Add location'.

8. Tap **Next** (E).

You have successfully logged into the Wiser app. Now, you can use the Wiser app to control devices and set up Devices and Rooms.


## App settings

An overview of the options available from the settings menu.

You can manage Account Settings, Location Settings, and Manage Users from the settings menu.

Tap **Settings** (A).

The **Settings** page appears.





The Setting page includes the following options:

<b>Information</b>	
<b>Privacy Dashboard</b>	Displays the Terms of Use and Privacy Notice.
<b>Profile</b>	Allows you to see the username and change it by tapping the Edit button.
<b>Email</b>	Displays the email ID information.
<b>Change password</b>	Allows you to change the password
<b>Settings</b>	
<b>Account Settings</b>	<p>Allows you to delete an account.</p> <p>Delete Account</p> <p><b>NOTE:</b></p> <ul style="list-style-type: none"> <li>Deleting your account is immediate and permanent.</li> <li>A deleted account cannot be restored.</li> <li>Deleting your account will log you out of your Wiser app and you will not be able to log in again. Make sure to decommission your devices first.</li> </ul>
<b>Location Settings</b>	Allows you to check the location-based energy consumption. Also, you can create and delete the location.
<b>Notify Me</b>	Allows you to receive the notifications.
<b>Manage Users</b>	Allows you to invite guests, friends, and family members by adding them as users, allowing access to devices or actions associated with your Wiser account. Also, you can remove from the users.
<b>Support</b>	
<b>Customer Support</b>	Allows you to contact customer support via email or by calling.
<b>Logout</b>	Allows you to logout from the Wiser app.

## User

### Adding a user

The Manage Users menu allows you to add new users and grant them access to devices or actions linked with your Wiser account.

1. Tap  **Settings**.
2. Tap **Manage Users**.

3. Tap **Add User**.

## 4. Enter a Username and Email ID.

5. Tap **Access time** and select any one of the following options from the dropdown menu:

- **From and To:** Allows you to select a specific time and date.
- **Permanent:** Allows you to select a permanent access.

**NOTE:** Enter a date and time when selecting **From and To**.

6. Tap **Add location**.

The **Select Location** page appears.

7. Select any of the listed locations and tap **Add**.

**TIP:** You can select multiple locations and provide respective access levels.

## 8. Select the access level (A) for the location from the following options:

- **No access:** You do not have any permission to control the device.
- **View access:** This allows you to view the devices.
- **Control access:** This allows you to control the device.

**NOTE:** When you select No access, you cannot choose a device from the devices list.

**TIP:** You can also set the access level for Security (C).

## 9. Select at least one device from the Devices (B) list.

10. Tap **Add User**.



An e-mail will be sent to the specified e-mail address.

#### 11. Tap **Done**.

You have successfully added the new user. Now, you can see the new user on the **Manage Users** page.

## Removing a user

You can remove a user from the Manage Users menu.


1. Tap  **Settings**.
2. Tap **Manage Users**.
3. On the top right corner of the screen, tap  **Edit**.
4. Tap the remove button next to the username and tap **Delete**.

You have successfully removed the user from the Manage Users menu.

## Location

### Adding a new location

You can add a new location from the Settings menu.



1. Tap  **Settings**.
2. Tap **Location Settings**.
3. On the bottom right corner of the screen, tap **+**.
4. Enter a new location name.
5. Tap **Add**.

**NOTE:** Alternatively, you can also create a new location from the  Hamburger menu > **+ Add Location**.

**TIP:** If you want to switch to another location, navigate to the Hamburger menu and select the location you want to switch.

### Removing a location

You can remove a location from the Settings menu.

1. Tap  **Settings**.
2. Tap **Location Settings**.
3. On the top right corner of the screen, tap  **Edit**.
4. Tap the remove button next to a location.
5. Tap **Delete**.

You have successfully removed the location.

## Energy

In the Energy Center, you can monitor your power grid in real-time, daily, over the last 7 days, monthly, and yearly. You can also access a detailed history of your grid and information on energy savings.

It provides detailed information on the annual bill.

**NOTE:** This energy data will only be populated if you have the EMD device in the Wiser App. Otherwise, you will not be able to see any energy-related data.


## Flow

The Flow tab shows the amount of power coming from the grid and how much is being consumed. You can filter it by Live, Date, Last 7 days, Month, and Year.

It displays you how much energy you are using in real-time, helps you use energy more efficiently, and controls appliances to reduce waste and save energy.

To navigate, tap **Energy**.

Tap **Flow (A)**.



## Insights


Insights provide users with detailed analytics and reports on their energy usage patterns, trends, and potential areas for improvement.

This information empowers users to make informed decisions about their energy consumption, identify opportunities for efficiency gains, and ultimately reduce their environmental impact and energy costs.

You can see where power is utilized more, check your usage summary, and track your carbon footprint all in one location.


To navigate, tap **Energy**.

Tap **Insights**




## Notifications

Notifications allow you to view messages related to your connected devices and keep informed about their status and activities.

1. Tap  **Settings**.
2. Tap the **Notify Me** toggle button.

**NOTE:** When you enable the **Notify Me** button, you can see notification messages on the **Dashboard** page.

3. Navigate to a **Dashboard** page.



4. On the top right corner of the screen, tap the **Notifications (A)** button. Now, you can see all messages related to devices.

## Changing the password

You can change a password from the Settings menu.

1. Tap  **Settings**.


2. Tap **Change password**.

**NOTE:** When changing the password, the new password should not match the previous 3 passwords.

3. Enter a current password.
4. Enter a new password.
5. Tap **Change password**.

## Deleting an account

You can delete an account from the Settings menu.

1. Tap  **Settings**.
2. Tap **Account Settings**.
3. Tap **Delete Account**.

**NOTE:**

- Deleting your account is immediate and permanent.
- A deleted account cannot be restored.
- Deleting your account will log you out of your Wiser app and you will not be able to log in again. Make sure to decommission your devices first.
- If you re-login within 7 days, you can restore the data.

4. Tap **Delete**.

You have successfully deleted an account.

## Customer support


Allows you to contact customer support via email or by calling.

Customer support allows you to address any issues, inquiries, or technical problems users may encounter while using the application. It includes email and direct contact with support representatives, aiming to ensure a positive user experience.

Tap  **Settings**.

Tap **Customer Support**.

Now, you can contact customer support via Email or by Call.

**TIP:** Alternatively, you can also navigate to  **Settings**, and on the top right corner of the screen, tap the customer support symbol.

## Cybersecurity principles

Following these cybersecurity principles may help to reduce the risk of cyber threats to the network where your system is installed.

- **Strong and Unique Passwords:** Use strong, unique passwords for your mobile app account and each connected device. Avoid using common or easily guessable passwords. Consider using a password manager to securely store your passwords.

- **Regularly Update Software:** Keep your mobile app, smartphone operating system, and smart home device firmware up to date. Updates often include security patches that address vulnerabilities and protect against potential threats.
- **Secure Network:** Ensure that your home Wi-Fi network is secured with a strong password and encryption (WPA2 or higher). Avoid using public Wi-Fi networks when interacting with your smart home app as they may be insecure and expose your data.
- **Two-Factor Authentication (2FA):** Enable 2FA if your smart home app supports it. This adds an extra layer of security by requiring a second verification step, such as a unique code sent to your mobile device, when logging in.
- **Only Download Official Apps:** Use official app stores (such as Google Play Store or Apple App Store) to download the mobile app for your smart home solution. Avoid downloading apps from unofficial sources, as they may contain malicious software.
- **Be Cautious with Permissions:** Review the permissions requested by the app during installation. Grant only the necessary permissions required for the app to function properly. Be cautious about granting unnecessary access to your device's location, camera, or microphone.
- **Regularly Review Connected Devices:** Periodically review the list of connected devices in your smart home app. Remove any devices that are no longer in use or unfamiliar to you, as they may pose a security risk.
- **Regularly Monitor Activity:** Keep an eye on the activity logs or notifications provided by the smart home app. Look for any suspicious or unauthorized access attempts, and report them to the app provider immediately.
- **Secure Physical Access:** Ensure that your smartphone and other devices used to control your smart home are protected with a lock screen or biometric authentication. This helps prevent unauthorized access in case of loss or theft.
- **Educate Yourself:** Stay informed about the latest cybersecurity best practices and potential threats related to smart home devices. Regularly update your knowledge to make informed decisions and protect your smart home ecosystem.

## Decommissioning a device

If you remove a device from your system to gift, resell, or otherwise dispose of, first remove any personally identifiable information from the device by performing a factory reset. This is especially important when decommissioning a system gateway. Refer to the particular device instructions for information on how to perform a factory reset.

# Safety Information

## Important Information

Read these instructions carefully and look at the equipment to become familiar with the device before trying to install, operate, service, or maintain it. The following special messages may appear throughout this manual or on the equipment to warn of potential hazards or to call attention to information that clarifies or simplifies a procedure.



The addition of either symbol to a “Danger” or “Warning” safety label indicates that an electrical hazard exists which will result in personal injury if the instructions are not followed.



This is the safety alert symbol. It is used to alert you to potential personal injury hazards. Obey all safety messages that accompany this symbol to avoid possible injury or death.

### **DANGER**

**DANGER** indicates a hazardous situation which, if not avoided, **will result in** death or serious injury.

**Failure to follow these instructions will result in death or serious injury.**

### **WARNING**

**WARNING** indicates a hazardous situation which, if not avoided, **could result in** death or serious injury.

### **CAUTION**

**CAUTION** indicates a hazardous situation which, if not avoided, **could result in** minor or moderate injury.

### **NOTICE**

NOTICE is used to address practices not related to physical injury.



# 16A 1M Connected Switch



CS16A1MSW

## For your safety

### **⚠ DANGER**

#### **HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH**

Safe electrical installation must be carried out only by skilled professionals. Skilled professionals must prove profound knowledge in the following areas:

- Connecting to installation networks.
- Connecting several electrical devices.
- Laying electric cables.
- Safety standards, local wiring rules and regulations.

**Failure to follow these instructions will result in death or serious injury.**

## About this product

16A 1M Connected Switch (hereinafter referred to as **switch**) is used to operate resistive, inductive or capacitive loads.

## Control options

**App control:** To control the switch through the Wiser app.

**Direct operation:** The switch can always be controlled manually.

## Installing the device

Refer to the installation instruction supplied with this product.  
See 16A 1M Connected Switch.


## Pairing the device

Connect your mobile device with your home Wi-Fi network and use the Wiser app to access and control it.


To pair the device:

**IMPORTANT:** Before pairing the device, connect your mobile to the home Wi-Fi network.

1. Open the Wiser app.
2. On the **Devices** page, tap **Devices**.
3. Tap **+** (A) to add a device.



The **Add Devices** page appears.




4. The **Add Devices** page includes the following tabs:

- **Preferred (B):** This tab allows you to select a device directly from the preferred list.
- **All (C):** This tab includes all available devices for you to select from.

**TIP:** You can select a device from either tab based on your preference.

- Select **Preferred** > **Smart Switch 16Amp (Wiser)**.
- Select **All** > **Switches and Controls** > **Wi-Fi Switches and Controls** > **Smart Switch 16Amp (Wiser)**.


5. Press the push button 4 times in 10 s.  
The LED indicator rapidly blinks green.




6. Tap **Next**.
7. Add the following Device Information:
  - **Enter Device Name (D)**: Add the device name.
  - **Assign Existing Room (E)**: Select an existing room.

**NOTE:** If your room is not in the existing room, create a new one.


  - **Add New Room (F)**: Create a new room.



8. Tap **Next**.  
**NOTE:** To begin scanning for devices, make sure to enable Bluetooth permissions.
9. Tap MAC ID (G).  
**NOTE:** If you are unable to find the device, tap **Rescan (H)**.



10. Tap **Select Wi-Fi (I)** and choose Wi-Fi network.



11. Enter the Wi-Fi password in the password field.

**NOTE:** After entering the password, the **Connect (J)** button will be enabled.

12. Tap **Connect (J)**.

Now, you can see the newly added device on the **Devices** page.


## Configuring the device

### Renaming the device

You can rename the device name using the Wiser app.

To rename the device:

1. On the **Devices** page, tap **Devices**.
2. Select the device for which you want to change the name.
3. On the top-right corner of the screen, tap **Settings (A)**.



4. Tap **Information**.

5. Enter the new name in the **Name (B)** field.

The screenshot shows the 'Settings' screen for a smart switch. The 'Name' field is highlighted with a red circle and the letter 'B'. The screen displays various settings including Information, Name, Change Room, Radio Type, Device Type, Device Details, Automate, Schedule, Voltage Detection & Load Cut-off, Thermal Cut-off, Notification, and Notify Me.

Settings	
Information	^
Name	✎
Change Room	Kitchen >
Radio Type	Wi-Fi
Device Type	Smart Switch 16Amp
Device Details	>
Automate	>
Schedule	>
Voltage Detection & Load Cut-off	>
Thermal Cut-off	>
Notification	
Notify Me	<input type="checkbox"/>

## Changing the device location

You can change the device location using the Wiser app.


To change the device location:

1. On the **Devices** page, tap **Devices**.
2. Select the device for which you wish to change the location.
3. On the top-right corner of the screen, tap **Settings**.
4. Tap **Information**.
5. Tap **Change Room (A)**.

The screenshot shows the 'Settings' screen for a smart switch. The 'Change Room' option is highlighted with a red circle and the letter 'A'. The screen displays various settings including Information, Name, Change Room, Radio Type, Device Type, Device Details, Automate, Schedule, Voltage Detection & Load Cut-off, Thermal Cut-off, Notification, and Notify Me.

Settings	
Information	^
Name	Geyser Switch ✎
Change Room	Kitchen >
Radio Type	Wi-Fi
Device Type	Smart Switch 16Amp
Device Details	>
Automate	>
Schedule	>
Voltage Detection & Load Cut-off	>
Thermal Cut-off	>
Notification	
Notify Me	<input type="checkbox"/>

6. Select the desired room from the list (B).




**NOTE:** If your room name is not present in the list. You can create a new room using the + (C).

## Adding devices to favourites

You can add devices to the favourites list using the Wisernet app.


To add favourites:

1. On the **Dashboard** (A) page, tap **Click here** (B) / **Add +** (C).



The **Manage Favourites** page appears.

2. Select a device from the list (D).



**NOTE:** You can select multiple devices as favourites.

3. Tap **Done** (E).


Now, you can see the devices on the **Dashboard** page.

## Removing devices from favourites

You can remove devices from the favourites list using the Wiser app.

To remove favourites:

1. On the **Dashboard** page, tap **Edit** (A).



The **Manage Favourites** page appears.

2. Unselect the device.
3. Tap **Done**.


## Creating a schedule

The device can be controlled and triggered by a schedule. Once the schedule is set, your system will follow the active schedule. You can create or modify the schedules at any time.

To create a schedule:


1. On the **Devices** page, tap **Devices**.

2. Select the device for which you want to create a schedule.
3. On the top-right corner of the screen, tap **Settings**.
4. Tap **Information > Schedules**.
5. On the top right corner of the screen, tap **+** to create a schedule.  
The **Add Schedule** page appears.
6. Add the following details when creating a schedule:
  - **Name (A)**: Enter a name for the schedule.
  - **On Time (B)**: Select the desired start time.
  - **Off Time (C)**: Select the desired end time.
  - **Weekdays (D)**: Select the schedule for weekdays.
  - **Weekend (E)**: Select the schedule for weekends.



**NOTE:** If you want to create a schedule on a specific day, select the day you want to schedule.

7. Tap **Add (F)**.  
The new schedule is added to the **Schedules** page.
8. Tap **Delete (G)** and then select **Ok** to delete a schedule.



9. Tap **Copy (H)** to reuse the same schedule.



10. Tap the toggle button (I) to turn on/off the schedule.


**NOTE:**

- You can edit the **On Time**, **Off Time**, and **Days** whenever you want to make changes.
- After editing the schedule, tap **Save**.

## Automate

Automate allows you to set the timing for when the device should be turned off and also set it to turn off when you are away.

1. On the **Devices** page, tap **Devices**.
2. Select the device.
3. Tap **Settings** > **Information** > **Automate**.
4. Tap the **Auto-Off Timer** (A) toggle button and set the time when the device should turn off.



5. Tap the **Away Mode** (B) toggle button to switch off the device when you are away.


**NOTE:** Use only one option at a time.

## Voltage detection & load cut-off

This smart feature enables you to set a voltage threshold. When the voltage drops below the set value, it automatically cuts the power supply, thereby protecting the device and extending its lifespan.

1. On the **Devices** page, tap **Devices**.
2. Select the device.
3. Tap **Settings** > **Information** > **Voltage Detection & Load Cut-off**.

4. Drag the green button to set the **Low Voltage Cut-off Value** (A).



**NOTE:** The recommended voltage is 180 V, with a minimum voltage of 90 V and a maximum value of 200 V.


5. Drag the green button to set the **High Voltage Cut-off Value** (B).

**NOTE:** The recommended voltage is 260 V, with a minimum voltage of 110 V and a maximum value of 300 V.

## Thermal cut-off value

This smart feature enables you to set a temperature value. When the temperature crosses the set value, it automatically cuts the power supply, thereby protecting the device and extending its lifespan.

1. On the **Devices** page, tap **Devices**.
2. Select the device.
3. Tap **Settings > Information > Thermal Cut-Off Value**.
4. Drag the green button to set the **Thermal Cut-Off value** (A).





**NOTE:** The default thermal cut-off value is set to 110 degrees.

## Removing the device

Using the Wiser app, you can remove a device from the device list.

To remove the device:


1. On the **Devices** page, tap **Devices**.
2. On the top right corner of the screen, tap  .  
The **Edit Device List** page appears.
3. Tap the remove button (A) which is next to the device name.



The message pop-up appears.

4. Tap **Delete** (B).
5. Tap **Delete Device** (C) and then select **Ok**.


**NOTE:** By removing the device, you will reset the device. If you still have a problem with the reset, then refer to [Resetting the device](#), page 27 .



## Resetting the device

You can reset the device to factory default manually.

Short-press the push button 14 times (<10 s).  
The LED blinks green after 10 s




**NOTE:** After reset, the device is ready for pairing.


## Changing the Wi-Fi access point

You can change the Wi-Fi network using the Wiser app.

1. On the **Devices** page, tap **Devices**.
2. Select the device.
3. Tap **Settings** > **Information** > **Device Details**.
4. Tap **Change Access Point** (A) to change the Wi-Fi network.




5. Select the Wi-Fi network.



**TIP:** If you can't find your Wi-Fi network, try tapping **Refresh** (B). If you still cannot find it, you can manually enter the SSID by tapping **Enter SSID** (C).

6. Enter the new Wi-Fi password in the password field (D).

**NOTE:** The **Connect** button will be enabled after entering the password.




7. Tap **Connect** (E).
8. Alternatively, you can also change the Wi-Fi access point manually by pressing the push button 8 times in 10 seconds.

## Changing the Wi-Fi access point while offline

When you change the SSID or password, the device goes offline. You can connect to a new Wi-Fi network without losing any previous data.

You can change the Wi-Fi network using the Wisernet app when the device is offline.

1. On the **Devices** page, tap **Devices**.
2. Select the device.
3. Tap **Settings > Information > Device Details**.
4. Tap **Change Access Point** (A) to change the Wi-Fi network.



5. Press the push button 8 times in 10 seconds.  
The LED indicator rapidly blinks green.
6. Tap MAC ID.

**NOTE:** If you are unable to find the device, tap **Rescan**.

It will redirect to the Wi-Fi network which is connected to the mobile.

7. Enter the new Wi-Fi password in the password field and tap **Connect**.


**NOTE:** The **Connect** button will be enabled after entering the password.

## Using the device

The Control Panel allows you to switch on/ off and control various settings. On the **Devices** page, tap **Devices** and select the device to access the control panel.

The control panel displays the following options:

- Power Now (W): Displays the load value of the device (A).
- Voltage (V): Displays the voltage of the device (B).
- Current (A): Displays the flow of electric current of the device (C).
- The current state of the device (F).
- Settings (D)
- Timeline (E)



## Switching On/Off the device manually

You can switch on/off the device manually. The device will provide power to the electrical appliance connected to it.

Short press the push button on the device once to switch on/off the 16A Switch .


**NOTE:** It is normal for the front surface of this product to become warm in use.

## Switching On/Off the device using the app


By using the Wiser app, you can switch on/off the device. To switch the device on/off:

1. On the **Devices** page, tap **Devices**.

2. Tap the power button (A) to switch on/off.



3. You can also switch on/off from the control panel by tapping the power button (B).



4. Alternately, you can also switch on/off from the **Dashboard** page when you add a device to the favourites list.

## Rooms


### Creating a new room

You can create a new room using the Wiser app.

To create a new room:

1. On the **Devices** page, tap **Rooms**.
2. Tap **+** to create a new room.  
The **Add Room** page appears.

3. Enter the room name in the name field (A).



4. Tap **Add Room** (B).


The new room is added to the **Rooms** page.

## Reassigning the device to a room

You can reassign a device to a room using the Wiser app.

To reassign:

1. On the **Devices** page, tap **Rooms**.
2. Select the room.
3. Tap **+** (A) to add a device.



4. Select a device from the **Devices** list.

**NOTE:** When you turn the room on/off (B), the devices that have been added to that room are activated.


## Renaming a room


You can rename a room using the Wiser app.

To rename:

1. On the **Devices** page, tap **Rooms**.
2. Select the room.



- On the top right corner of the screen, tap .
- Enter the new name in the **Room Name (A)** field.





- On the top right corner of the screen, tap **Done (B)**.  
**NOTE:** You can also delete the room by using the **Delete Room (C)** button.

## Deleting a room

You can delete a room using the Wiser app.

To delete:

- On the **Devices** page, tap **Rooms**.
- On the top right corner of the screen, tap .
- The **Edit rooms list** page appears.
- Unselect (A) the room.



- Tap **Delete (B)**.

## Notifications

The app will send notifications related to your device when you enable the notification button.

- On the **Devices** page, tap **Devices**.

2. Select the device.
3. Tap **Settings > Notification**.
4. Tap the **Notify Me** toggle button to receive notifications.


**NOTE:** Tapping the notification icon on the **Dashboard** page allows you to view all notifications.

5. Tap **Other Notifications**. The **Other Notifications** include the following options:
  - **Standby Notification (A):** Tap the **Standby Notification (A)** toggle button to receive notifications when a device is consuming less than the standby value.

**NOTE:** The maximum value you can set is 200 watt.

- **Usage Reminder (B):** Tap the **Usage Reminder (B)** toggle button to receive notifications when a device is on for more than the set time.

**NOTE:** You can set the time by tapping the time.




## History

The history tab provides a record of past activities and actions of the device in the Wiser app. It displays the date, time, and action.

1. On the **Devices** page, tap **Devices**.
2. Select the device.
3. Tap **Settings > History**.  
You can see the history of the device.

4. Tap the refresh button (A) to get the latest results.




Settings	
Notification	
History	
02 Nov 2023 15:41:47	TURNED ON Status
02 Nov 2023 15:41:47	TURNED ON Status
02 Nov 2023 17:57:45	TURNED OFF Status
02 Nov 2023 17:57:45	TURNED OFF Status
02 Nov 2023 11:53:12	TURNED ON Status
02 Nov 2023 11:53:12	TURNED ON Status
02 Nov 2023 11:53:11	TURNED OFF Status
02 Nov 2023 11:53:11	TURNED OFF Status
02 Nov 2023 11:52:51	TURNED ON Status
02 Nov 2023 11:52:51	TURNED ON Status

## Timeline

The timeline page displays the device's total energy consumption in kilowatt-hours (kWh) over several time intervals such as the hour, day, last 7 days, month, and year. This allows you to track and analyze your energy usage patterns over a specific time.


1. On the **Devices** page, tap **Devices**.
2. Select the device.
3. On the top right corner of the screen, tap **Timeline** (A).



The **Timeline** page appears.

4. The timeline displays the following options:

- **Live (B)**: Display the Voltage, Current, Total Energy, Power, Apparent Power, and Power Factor.
- **Hour (C)**: Displays the total consumption for the selected hour. You can select the time and date by tapping the time and date.
- **Day (D)**: Displays the total consumption for the selected day. You can select the day by tapping the day.
- **Last 7 Days (E)**: Displays the total consumption for the past 7 days.
- **Month (F)**: Displays the total consumption for the selected month. You can select the desired month by tapping the month.
- **Year (G)**: Displays the total consumption for the selected year. You can select the year by tapping the year.




## Quick (Action)

An action allows you to group multiple actions that are usually done together. Using the Wiser app, you can create actions based on your needs (such as movie night).

To create an action:


1. On the **Actions** page, tap **Quick**.
2. Tap **+** to create an action.

The **Add Action** page appears.




3. The **Add Action** page includes the following options:
  - **Add a Sequence (A)**: Switch on multiple devices in a sequence.
  - **Add Quick Action (B)**: Switch on multiple devices at a time.
4. Tap **Add a Sequence (A)** or **Add Quick Action (B)**.
 

**TIP:** Follow the same steps to create an action for both **Add a Sequence (A)** and **Add Quick Action (B)**.
5. Tap **Add Device (C)** and select the device with its respective options from the Devices list (D).




6. After selecting the device, tap **Done (E)**.




**TIP:** Repeat steps 5 and 6 to add more than one device.

**NOTE:** You can change the waiting time by tapping the time (F) (Only for Add a Sequence).

7. Enter the **Action Name** (G).8. Tap **Icon** (H) and select the icon from the list.9. Tap **Notification** (I) and enable the toggle button for the following options and then tap **Save** (K):

- **Show timeline:** Displays the total power consumption.
- **Push notifications:** Receives the notifications.




**NOTE:** To switch the toggle buttons, make sure to first activate the **Notify me** toggle button on the settings page.

10. Once all the actions are set, on the top right-corner of the screen, tap **Save** (J).

You can see the newly created action on the **Quick** page.

## Editing an action

To edit an action:


1. On the **Actions** page, tap **Quick**.
2. On the top right corner of the screen, tap . The **Edit Actions List** page appears.
3. From the **Edit Actions List** page, tap the action you want to edit.
 

**TIP:** If you want the same action, tap the hand symbol, it will copy the same action and add it to the **Edit Actions List**.
4. Tap each item (such as add, remove, rename, etc.) to update.

5. Once all the edits are done, tap **Update**.

## Deleting an action


To delete an action:


1. On the **Actions** page, tap **Quick**.
2. On the top right corner of the screen, tap .  
The **Edit Actions List** page appears.
3. On the **Edit Actions List** page, tap the remove button that is next to the action, and then tap **Delete** to remove it.

## Creating an automation for trigger


Automation allows you to group multiple actions that are usually done together, triggered automatically or at scheduled times. By using the Wiser app, you can create automation based on your needs.

1. On the **Actions** page, tap **Trigger**.
2. Tap **+** (A) to create an automation.



3. Tap **Add Trigger** (B).

The **Select Trigger** page appears.

4. Select a trigger option from the following list on the **Select Trigger** page:

- **Time** (D)
- **Location** (E)
- **Device** (F)
- **Power** (G)
- **Weather** (H)

5. Tap **Time** (D), select any one of the following options:

- **Any time**: Set for any time.
- **At Specific time**: Set for a specific time.
- **At in between time**: Set for in between time.
- **Perform only once**: Set for only once.

**NOTE:** Tap the toggle button and then tap **Save**.

6. Tap **Location** (E), select any one of the following options:


- **Arriving location**: Select arriving location.
- **Departing location**: Select a departing location.

**NOTE:** Mobile location should turn on.

7. Tap **Device** (F) and select a device from the list.




8. Tap **Power (G)** and select an option from the following list:
  - **Home EMD**
  - **Home EMD2**
9. Tap **Weather (H)** and select an option from the following list:
  - **Outside Temperatures**
  - **Outside Humidity**
  - **When Sunrises**
  - **When Sunsets**
10. Tap **Add Device (C)** and select the device with its respective options from the Devices list (I).



11. After selecting the device, tap **Done (J)**.


**TIP:** Repeat steps 10 and 11 to add more than one device or action.



12. Enter the **Action Name**.
13. Tap **Icon** and select the icon from the list.
14. Tap **Notification** and enable the toggle button for the following options:
  - **Show timeline:** Displays the total power consumption.
  - **Push notifications:** Receives the notifications.
15. Once all the actions are set, tap **Save**.  
You can see the newly created automation on the **Trigger** page.


## Editing a trigger

To edit a trigger:

1. On the **Actions** page, tap **Trigger**.
2. On the top right corner of the screen, tap .  
The **Edit Actions List** page appears.
3. On the **Edit Actions List** page, tap the trigger you want to edit.  
**TIP:** If you want the same trigger, tap the hand symbol, it will copy the same trigger and add it to the **Edit Actions List**.
4. Tap each item (such as add, remove, rename, etc.) to update.
5. Once all the edits are done, tap **Update**.





## Deleting a trigger

To delete a trigger:



1. On the **Actions** page, tap **Trigger**.
2. On the top right corner of the screen, tap  to remove a trigger.  
The **Edit Actions List** page appears.
3. On the **Edit Actions List** page, tap the remove button that is next to the trigger, and then tap **Delete** to remove it.

## LED indication

### Pairing

User Action	LED Indication	Status
Press the push-button 4 times in 10 s.	Blinking green rapidly. 	Pairing mode is active for 3 minutes. When pairing is completed, the LED will display a solid green if a device is ON; otherwise, no LED will be displayed. 
Press the push-button 8 times or 4 ON cycles in 10 s to change the Wi-Fi access point mode.	Blinking green rapidly. 	Change AP mode is active for 3 minutes. When the change AP is completed, the LED will display solid green if a device is ON; otherwise, no LED will be displayed. 


### Resetting

User Action	LED Indication	Status
Press the push-button 14 times or 7 ON cycles in 10 s.	Blinking green rapidly. 	Pairing mode is active for 3 minutes. When pairing is completed, the LED will display a solid green if a device is ON; otherwise, no LED will be displayed. 

### LED Indicator Mode

LED Indicator Mode	LED Indication
Always Off	No LED
Always On	Solid green

**LED Indicator Mode (Continued)**

	
Device disconnected from the router after pairing	No LED
OTA update	No LED
Reset state / Not paired / Not added	No LED

## Troubleshooting

Symptom	Solution
The device is not ready to pair after the device is removed from the app.	Reset to factory default settings, refer to resetting the device, page 27.
If the device is offline in the app.	The Wi-Fi credentials may have changed. Refer to Changing the Wi-Fi access point, page 28 to update the Wi-Fi credentials.
If the device is not responding by physical operation.	Reboot the device by switching off the MCB for 3 seconds, then switching it back on.
If the device is not responding in the App.	Reboot the device. If the issue is still not resolved, connect with customer care.

## Technical data

**Technical**

Nominal voltage	AC 110 - 230 V
Frequency	50 - 60 Hz
Max. Current	16 A
Max. Load	3000 W (Resistive) <b>Note:</b> Widely supports most of the home appliances like Geyser, AC, Refrigerator, LED and fluorescent lamps etc. - Subject to Power factor.
Connection	Line/Phase & Load: 2.5 mm <sup>2</sup> Neutral: 1.5 mm <sup>2</sup>
Energy monitoring	Yes
Neutral conductor	Mandatory
Operating temperature	- 5° C to + 45° C
Over load protection	Yes
Sustained surge protection	Yes
Relative humidity	10 % to 95 %
Wi-Fi Range	Up to 30 m
Wire nut type	2299505 (TE)
<b>Compliance</b>	
Radio/RF	ETSI EN 300 328
Communication interface	Wi-Fi®: 2.4 GHz only, IEEE 802.11 b/g/n

## Trademarks

- Wiser™ is a trademark and the property of Schneider Electric SE, its subsidiaries and affiliated companies.
- Wi-Fi® is a registered trademark of Wi-Fi Alliance®.
- Apple® and App Store® are brand names or registered trademarks of Apple Inc.
- Google Play™ Store and Android™ are brand names or registered trademarks of Google Inc.

Other brands and registered trademarks are properties of their relevant owners.



Schneider Electric India Pvt Ltd  
C 56, Mayapuri Industrial area Phase-11  
110064 New Delhi  
India

1800 103 0011

[www.se.com](http://www.se.com)

As standards, specifications, and design change from time to time,  
please ask for confirmation of the information given in this publication.

© 2024 – 2024 Schneider Electric. All rights reserved.

DUG\_16A Connected Switch-01