

ELKO - Smart Radiator Thermostat

Wiser Home Device user guide

Information about features and functionality of the device.

10/2025



Legal Information

The information provided in this document contains general descriptions, technical characteristics and/or recommendations related to products/solutions.

This document is not intended as a substitute for a detailed study or operational and site-specific development or schematic plan. It is not to be used for determining suitability or reliability of the products/solutions for specific user applications. It is the duty of any such user to perform or have any professional expert of its choice (integrator, specifier or the like) perform the appropriate and comprehensive risk analysis, evaluation and testing of the products/solutions with respect to the relevant specific application or use thereof.

The Schneider Electric brand and any trademarks of Schneider Electric SE and its subsidiaries referred to in this document are the property of Schneider Electric SE or its subsidiaries. All other brands may be trademarks of their respective owner.

This document and its content are protected under applicable copyright laws and provided for informative use only. No part of this document may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Schneider Electric does not grant any right or license for commercial use of the document or its content, except for a non-exclusive and personal license to consult it on an "as is" basis.

Schneider Electric reserves the right to make changes or updates with respect to or in the content of this document or the format thereof, at any time without notice.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any errors or omissions in the informational content of this document, as well as any non-intended use or misuse of the content thereof.

Table of Contents

Safety Information.....	4
About the Document.....	5
ELKO - Smart Radiator Thermostat.....	8
About the device.....	8
Installing the device	9
Pairing the device with the Wiser hub	9
Configuring the device	12
Setting the device location	12
User interface lock settings.....	13
Identifying the device	13
Calibrating the device.....	15
Using the device.....	15
Setting the room temperature manually	15
Operating the device using the Wiser Home app	17
Setting the room temperature using the app.....	17
Creating a Schedule/Event	20
Editing Schedule/Event	23
Built in Automation	24
Voice control.....	27
Creating a moment	28
Creating an automation	32
Removing the device	40
Resetting the device	41
Replacing the batteries	42
LED indications	43
Troubleshooting	44
Technical Data	44

Safety Information

Important Information

Read these instructions carefully and look at the equipment to become familiar with the device before trying to install, operate, service, or maintain it. The following special messages may appear throughout this manual or on the equipment to warn of potential hazards or to call attention to information that clarifies or simplifies a procedure.



The addition of either symbol to a “Danger” or “Warning” safety label indicates that an electrical hazard exists which will result in personal injury if the instructions are not followed.



This is the safety alert symbol. It is used to alert you to potential personal injury hazards. Obey all safety messages that accompany this symbol to avoid possible injury or death.

DANGER

DANGER indicates a hazardous situation which, if not avoided, **will result in** death or serious injury.

Failure to follow these instructions will result in death or serious injury.

WARNING

WARNING indicates a hazardous situation which, if not avoided, **could result in** death or serious injury.

CAUTION

CAUTION indicates a hazardous situation which, if not avoided, **could result in** minor or moderate injury.

NOTICE

NOTICE is used to address practices not related to physical injury.

About the Document

Document Scope

This document provides instructions for installing, configuring, and operating the ELKO Smart Radiator Thermostat using the Wiser Home app. It explains how to pair the device with the hub, set room temperature manually or via app, create schedules and automations, and use voice control with Alexa or Google Home. Users can manage device settings, create moments for grouped actions, and monitor or adjust heating based on room conditions. The guide also includes steps for resetting the device, replacing batteries, and troubleshooting common issues, along with technical specifications and LED behavior indicators.

Validity Note

The characteristics of the products described in this document are intended to match the characteristics that are available on elko.no. As part of our corporate strategy for constant improvement, we may revise the content over time to enhance clarity and accuracy. If you see a difference between the characteristics in this document and the characteristics on elko.no, consider elko.no to contain the latest information.

For your safety

<i>NOTICE</i>
RISK OF DAMAGE TO DEVICE • Make sure that the O-ring is seated firmly on the thread. • The ring nut should be tightened by hand, do not use any tools. Do not tighten too hard. Failure to follow these instructions can result in equipment damage.

General Cybersecurity Information

In recent years, the growing number of networked machines and production plants has seen a corresponding increase in the potential for cyber threats, such as unauthorized access, data breaches, and operational disruptions. You must, therefore, consider all possible cybersecurity measures to help protect assets and systems against such threats.

To help keep your Schneider Electric products secure and protected, it is in your best interest to implement the cybersecurity best practices as described in the [Cybersecurity Best Practices](#) document.

Schneider Electric provides additional information and assistance:

- [Subscribe to the Schneider Electric security newsletter.](#)
- [Visit the Cybersecurity Support Portal web page to:](#)
 - [Find Security Notifications.](#)
 - [Report vulnerabilities and incidents.](#)
- [Visit the Schneider Electric Cybersecurity and Data Protection Posture web page to:](#)
 - [Access the cybersecurity posture.](#)
 - [Learn more about cybersecurity in the cybersecurity academy.](#)
 - [Explore the cybersecurity services from Schneider Electric.](#)

Environmental Data

Find and download comprehensive environmental data about your products, including RoHS compliance and REACH declarations as well as Product Environmental Profile (PEP), End-of-Life instructions (EOLi) and much more.

<https://www.se.com/myschneider>



General information about Schneider Environmental Data Program

Click the link below to read about Schneider Electric's Environmental Data Program.

<https://www.se.com/ww/en/about-us/sustainability/environmental-data-program/>



Declaration of Conformity

Hereby, Schneider Electric Industries SAS, declares that this product is in compliance with the essential requirements and other relevant provisions of RADIO EQUIPMENT DIRECTIVE 2014/53/EU.

Declaration of conformity can be downloaded on:

- <https://www.go2se.com/ref=EKO09765>

Available Languages of the Document

The document is available in these languages:

- English
- Norwegian

Information on Non-Inclusive or Insensitive Terminology

As a responsible, inclusive company, Schneider Electric is constantly updating its communications and products that contain non-inclusive or insensitive terminology. However, despite these efforts, our content may still contain terms that are deemed inappropriate by some customers.

Trademarks

- Zigbee® is a registered trademark of the Connectivity Standards Alliance.
- Wiser™ is a trademark and the property of Schneider Electric, its subsidiaries and affiliated companies.
- *QR Code* is a registered trademark of DENSO WAVE INCORPORATED in Japan and other countries.

Other brands and registered trademarks are the property of their respective owners.

ELKO - Smart Radiator Thermostat



EKO09765

Related Topics

- About the device
- Installing the device
- Pairing the device with the Wiser hub
- Configuring the device
- Using the device
- Removing the device
- Resetting the device
- Replacing the batteries
- LED indications
- Troubleshooting
- Technical Data

About the device

The Smart Radiator Thermostat (hereinafter referred to as **Thermostat**) uses integrated temperature sensors to control the flow of water through a radiator, thereby regulating the temperature in a room. The target temperature and the switching times are set in the Wiser Home app.


Personalize your home heating by adding a Thermostat to your Wiser Home system. This provides an effortless control to set different schedules and temperatures in different rooms, and upgrading to room-to-room heating control could save energy usage. Thermostats provide ultimate comfort, convenience and practicality.

Intended use:

- Individual room control
- Mobile control anytime, anywhere with the Wiser Home app
- Boost mode for ease and comfort.

Diagram of operating elements

- A. 3 status LEDs
- B. Twistable cap
- C. Chrome ring nut.



Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)

Installing the device

Refer to the installation instruction supplied with this product.
See [Smart Radiator Thermostat](#).

Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)

Pairing the device with the Wiser hub

Using the Wiser Home app, pair your Thermostat with the **Wiser Hub** to access and control.

To pair the Thermostat:


1. On the **Home** screen, tap .
2. Tap **Devices** >  and tap **Climate** > **Radiator Thermostat**.

TIP:


- You can also navigate by tapping **Control** >  > **Climate** > **Radiator Thermostat**.
- The next screen shows the joining process of the Thermostat.

3. Twist and hold the Thermostat cap in the “+” direction.

After 3 seconds, LED flashes green.




In the app, you can see the Thermostat is successfully joined.



4. Tap **Next** to enter Thermostat name and assign to an existing room or a new room.

After you pair the device, a success screen appears with the following options:

- **+ Add New Device:** Tap to continue pairing more devices.
- **Start Using Your Device:** Tap to start using the paired device.



NOTE: The success screen appears only if you are logged in as a **Home Owner**.

The Thermostat is now listed on the **Control** tab under the **All** and the specific room tabs.

Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)

Configuring the device

IMPORTANT: The temperature data from the sensor will be used as an input for the heating system of the room. If a room has multiple temperature measuring devices (Room Thermostat, Smart ZB Thermostat 16 A, or SmartSensor Climate Wireless), the system calculates the average temperature measured from the devices to control the heating based on the overall temperature of the room.

For more details, refer to the [Setting the device as temperature source](#).


Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)
- [Setting the device location](#)
- [User interface lock settings](#)
- [Identifying the device](#)
- [Calibrating the device](#)

Setting the device location

You can add your device to any room (such as bedroom, living room, dining room etc.).

1. On the **Home** screen, tap .
2. Tap **Devices**, select the device from the list for which you wish to change the location.
3. Tap **Location**  to open setup screen.
4. On the **Device Setup** screen, you can enter **New room name** (A) or select an existing room from the list (B).



TIP: If the device is already assigned, you can remove it from the existing room. Tap **Remove from Room** (C).

5. Once changes are done, tap **Submit** (D).

Related Topics

- Configuring the device (Parent Topic)


User interface lock settings

Using the Wiser Home app, you can lock the Thermostat controls (nothing will happen when the Thermostat cap is twisted in either the + or – direction). This prevents children from changing the temperatures in your room by playing with the Thermostat.

To lock or unlock the Thermostat control:

1. On the **Home** screen, tap .
2. Tap **Devices > Radiator Thermostat > Device lock** toggle switch (A) to lock or unlock the Thermostat control.

TIP: When the Thermostat lock is active, a  (B) will appear next to Thermostat.



Related Topics

- Configuring the device (Parent Topic)

Identifying the device

Using the Wiser Home app, you can identify a Thermostat from the other available devices in the room.


To identify the Thermostat:

1. On the **Home** screen, tap .

2. Tap **Devices > Radiator Thermostat > Identify** (A).

NOTE:

- This feature flashes the Thermostat LEDs, so you can identify the actual device. It may take up to a minute to start and flash the Thermostat LED.
- The Thermostat LEDs will continue to flash until you tap **OK**.



Related Topics

- [Configuring the device \(Parent Topic\)](#)

Calibrating the device

The Thermostat calibrates the radiator valve, it adjusts the pin position, automatically after 5 minutes when batteries are inserted. It takes only a few seconds to do the calibration. You can hear the motor running sound when the Thermostat starts calibrating.

Related Topics

- [Configuring the device \(Parent Topic\)](#)

Using the device

Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)
- [Setting the room temperature manually](#)
- [Operating the device using the Wiser Home app](#)
- [Setting the room temperature using the app](#)
- [Creating a Schedule/Event](#)
- [Editing Schedule/Event](#)
- [Built in Automation](#)
- [Voice control](#)
- [Creating a moment](#)
- [Creating an automation](#)

Setting the room temperature manually


The room temperature can be increased/decreased manually by twisting the cap of the Thermostat.

Twist the Thermostat cap:

- In the “+” direction to increase the temperature. The red LED will light up for 5 seconds.
- In the “-” direction to lower the temperature. The blue LED will light up for 5 seconds.

When the Thermostat cap is twisted, the set-point temperature is increased/decreased by 2 °C from the current room temperature. The boost is active for 1 hour.

NOTE: If the set-point temperature is already more than 2 °C above or below the room temperature, a boost will not change the set-point temperature.



Related Topics


- Using the device (Parent Topic)

Operating the device using the Wiser Home app

In the Wiser Home app, the device control screen allows to switch ON/OFF the device and control it.

On the **Control** tab, select the thermostat.

The device control screen displays the following options:



A	Tap the toggle switch allow the system to follow a schedule.
B	Tap to redirect you to the Schedule screen, where you can create a schedule.
C	Tap to add the device to the Favorite devices section in the Home screen. When you add it to your Favourites . To know more about Favourites , refer to the Managing Favourites topic in the respective System User Guide.
D	Tap to control various settings from the Device Settings screen.
E	Tap to manually turn the device ON/OFF.

Related Topics

- Using the device (Parent Topic)

Setting the room temperature using the app


Using the Wiser Home app, you can adjust, set or boost the room temperature.

Precondition: Add a ELKO - Wiser Room Thermostat/ELKO - SmartSensor Climate Wireless in the same room where Thermostat is located.

To adjust, set or boost the room temperature:


1. On the **Control** tab, tap **All** devices or a room tab where the Thermostat is located.
 - a. Use the slider control on the right of the screen to adjust the temperature.

NOTE: The flame shows that the room temperature is lower than the desired temperature (set point) and so the heating is ON.



IMPORTANT:

- When the boost time is set, the system automatically increases the set-point temperature by 2 °C for the duration of the boost. Once the boost period ends, the temperature returns to the last set-point.
- Moving the slider control to the bottom of the bar activates **Frost Protection** mode. In this mode, the system maintains the room temperature at a constant 5 °C to prevent freezing.



TIP: You can also adjust the room temperature:

- By tapping  or  on the **Control** tab, in the  **Heating** section of the concerned room to adjust its temperature.

NOTE: If you only have a single device in the Wiser System, the **Control** tab will not be visible. All functions will be accessible through the **Home** screen.

- b. Tap  to set the boost time.

IMPORTANT: Once the boost time is set, the set-point temperature automatically increases by 2 °C for the set boost time. After the boost

time is over, the set-point temperature returns to the current scheduled event or to the previous set-point temperature.

NOTE: Boost can be stopped at any time by tapping the  and selecting it **off**.

Related Topics


- Using the device (Parent Topic)

Creating a Schedule/Event

The device can be fully controlled and triggered by a schedule. Once the schedule is set, your system will follow the active schedule. You can create or modify the schedules at any time.

To create the schedule/event:

1. On the **Home** screen, tap .
2. Tap on the **Schedules** tab > .
3. On the **New Schedule** page, enter the **Schedule name**, select **Type**, and select room.
4. Tap **Create**.



The screenshot shows the 'New Schedule' form with the following fields and options:

- NAME**: A text input field with the placeholder 'Schedule name'.
- TYPE**: A dropdown menu with 'Climate' selected and 'Lights' as an option.
- APPLIES TO**: A list of rooms with checkboxes. 'Living Room' and 'Bedroom' are both checked.
- Create**: A green button at the bottom.

5. Select any day (A) and tap  for add event:

- Select temperature (for example 16 °C).


NOTE: When you put the slider control at the bottom of the bar for the schedule, the Frost Protection mode is activated when the schedule begins.

In the frost protection mode, the system maintains the room temperature at 5 °C.

- Set time (for example 12:00).

NOTE: A maximum of 8 events can be created per day.

You can tap  to copy the schedule from one day to other days or copy the entire schedule to a new schedule or to an existing one.




6. Tap **Set**.

7. On the top right corner of the screen, tap  and select **Follow schedule** toggle switch to turn on/off the schedule.

When your system is following a schedule:

The new set point will continue to be active until the next scheduled event.

You can see the until time on the **Control** tab under the device name. The until time shows the time till which the schedule is set to ON.



When your system is not following a schedule:

Any set-point changes made with the slider will continue to be active until the next time the slider is used.

The until time disappears from the screen.


Related Topics

- Using the device (Parent Topic)

Editing Schedule/Event

To edit the schedule:

1. On the **Home** screen, tap .
2. Tap **Schedules** tab and select the Schedule that you want to modify.
3. Tap **SCHEDULE DETAILS** to do any of the following:
 - To rename the device
 - To change the device location
 - To delete Schedule
4. To edit the **EVENTS**, select a day, and tap  to change the time and temperature.



< Living Room

SCHEDULE DETAILS ▾

Type

Edit Event

TEMPERATURES

18.5°

19°

19.5°

WHEN

05 29

06 : 30

07 31

Cancel Delete Set

Off 07:30

Related Topics

- Using the device (Parent Topic)

Built in Automation


There are three built in Automation such as Boost All, Cancel all overrides and Away mode.

Related Topics

- Using the device (Parent Topic)
- Boost All
- Cancel all overrides
- Away Mode

Boost All

You can apply a boost of +2 °C for 1 hour to every room in the system. It won't affect hot water in any way. As this is a "one-time action", you can find Boost All (A) in the "Automation" menu by clicking the "Automation" tab at the bottom of the **Home** screen.




Related Topics

- Built in Automation (Parent Topic)

Cancel all overrides

The Cancel all overrides (A) will put all the heating back under 'system control' meaning that if you've selected Boost All or even if you've boosted or manually overridden a room setpoint individually, this will cancel the override and put all the rooms back to their scheduled set points. You can find it in the "Automation" menu by tapping the "Automation" tab at the bottom of the **Home** screen.



Related Topics

- Built in Automation (Parent Topic)

Away Mode


When Away Mode (A) is activated, all rooms will be set to the Away temperature (default 16 °C). It will show a checkmark in the “Automation” page when active. You can find it in the “Automation” menu by tapping the “Automation” tab at the bottom of the **Home** screen.

When Away mode is active, only rooms that have set point temperatures higher than the Away mode temperature will be affected. For example, if a given room is set to 5 °C, Away mode will not force it to the Away temperature.

While Away Mode overrides Boost and rooms that are and aren't following a schedule, it is still possible to manually change the set-point temperature and boost individual rooms after activating Away Mode. It is also possible to boost or manually turn the hot water ON.

All rooms and hot water will display their Away mode values. The hot water will be turned OFF if you have activated this option on the Away Mode screen.

NOTE: The current temperature will not be displayed when away mode is activated.



Related Topics

- Built in Automation (Parent Topic)

Voice control

You can control the plug using Amazon Alexa® and Google home by giving a voice command.

Amazon Alexa™

Amazon Alexa™ (Alexa) is an intelligent personal assistant developed by Amazon™, and is capable of voice interaction.

Common Wiser commands for Alexa

- Discover Devices: “Alexa, discover devices”
- Reduce Temperature: “Alexa, decrease the temperature upstairs by 4 degrees”
- Increase Temperature: “Alexa, increase the temperature upstairs by 3 degrees”
- Set Temperature: “Alexa, set the upstairs to 20 degrees”
- Get Temperature: “Alexa, what is the upstairs temperature?”
- Get the Set Point: “Alexa, what is the upstairs set to?”

Related Topics

- Voice control (Parent Topic)

Google Home™

Google Home™ is a brand of smart speakers that work similarly to Amazon's Alexa. The user can speak a profusion of commands to request information, or ask Google Assistant to perform action.”

Common Wiser commands for Google Home™:

- Inquiry: “OK, Google, is the hot water on?”
- Hot Water Command: “OK, Google, turn on/off the hot water”
- Room Temperature: “OK, Google, how warm is (room name)?”
- Set Temperature: “OK, Google, set (room name) to XX degrees”
- Increase Temperature: “OK, Google, increase the setpoint by XX degrees”
- Set Temperature: “OK, Google, set (room name) to XX degree”

Changes made with Google Home™

All changes made through a voice command related to radiator thermostat that is valid for one hour, or until the next scheduled event. The user cannot change this action. This also applies for boosts initiated from the radiator thermostat.

Related Topics

- Voice control (Parent Topic)

Creating a moment


A Moment allows you to group multiple actions that are usually performed together. By using the Wiser Home app, you can create moments based on your needs.

To create a moment:


1. On the **Home** screen, tap .
2. Go to **Moments** >  to create a moment.
3. Enter the name of the moment (A).

TIP: You can choose the cover image that best represents your moment by tapping .

4. Tap **Add actions** (B) to select the list of devices.



5. In the **Add actions** menu, you can select the devices (C).




6. Once all the device are selected, tap **Done**.

7. On the **Moment creator** page, tap the device to set the condition. For example, select heating.

- Set the required temperature using sliding control (D).

NOTE: When you put the slider control (D) at the bottom of the bar for the moment, the Frost Protection mode is activated. In the frost protection mode, the system maintains the room temperature at 5 °C.



When the desired condition is set, tap **Set**.

8. Once all conditions are set, tap **Save**.

Once the moment is saved, it is visible on the **Moments** tab. You can tap on the moment to enable it.

TIP:


- If you want to see the created moments on the **Home** screen, go to **Home** > > **Home** screen > **Moments**. Enable the toggle button to view moments on the **Home** screen.
- You can also rearrange the moments by tapping **Edit** from the **Moments** tab on the **Home** screen, or by tapping **Automation** > **Moments** > **Reorder**.

Related Topics

- Using the device (Parent Topic)
- Editing a moment
- Deleting a moment

Editing a moment

1. On the **Home** screen, tap **Automations** .
2. Go to **Moments**, locate the moment you want to edit and tap .
3. On the **Moment editor** screen, you can perform following changes:
 - Change the icon .
 - Rename the moment.
 - Tap each action to change the settings.
 - To remove an action, slide the action to the left and then tap  (A) to delete it.
 - Tap  **Add actions** (B) to add new action.



4. Tap **Save** to save the changes.


Related Topics

- Creating a moment (Parent Topic)

Deleting a moment

1. On the **Home** screen, tap **Automations** .
2. Go to **Moments**, locate the moment you want to delete and tap .

3. On the **Moment editor** screen, tap **Delete** (A) and then tap **OK** (B).



Related Topics

- Creating a moment (Parent Topic)

Creating an automation

An automation allows you to group multiple actions that are usually done together, triggered automatically or at scheduled times. By using the Wiser Home app, you can create automations based on your needs.


1. On the **Home** screen, tap .

2. Go to **Automation** >  to create an automation.

NOTE: Maximum 10 automations can be added.

3. Tap **If** (A) and select any of the following conditions (B):


- **All conditions:** This triggers an action only when all conditions are met.
- **Any condition:** This triggers an action when at least one condition is met.



4. Tap **Add conditions** and select any of the following (C):


- **Device status change:** Select a device to enable automation.
- **Away Mode:** Enable/Disable away mode to trigger an action.

TIP: Away mode can also be used as a trigger to turn off the lights, dimmer or closing the shutter etc. For more information about , refer to the system user guide.



5. Tap **Device status change** > . Set the temperature using sliding bar (D) and select the condition (E) (less than / more than), then tap **Set**.

NOTE: When the slider control is set to the bottom for the automation, Frost Protection mode is automatically activated at the start of the automation. In this mode, the system maintains the room temperature at 5 °C to prevent freezing.




NOTE:

- Maximum 10 conditions can be added.

- To remove an added condition, swipe left and tap .

6. To set a specific time for your automation, tap **When** > **Add time** and select any of the following (F):
- **Specific time of the day: Sunrise, Sunset, Custom.**
 - **Period of time: Daytime, Night time, Custom.**




NOTE:


- Maximum 10 entries can be added

- To remove a specific time, swipe left and tap .


7. To add an action, tap **Then > Add an action** and select any of the following (G):
- **Control a device:** Select a devices that you want to trigger.
 - **Send notification:** Turn on the notification for the automation.
 - **Activate a moment:** Select the moment that you want to trigger.
 - **Wait:** This option allows you to add a delay in an automation sequence. You can set the wait time in increments of 1 hour and 1 minute, up to a maximum of 24 hours. This feature is useful for delaying actions within an automation.



8. Tap **Control a device > Heating** and select any of the following (H):
- **Boost:** Set the duration to increase the temperature by 2 °C.
 - **Setpoint:** Set the desired temperature.



9. Tap **Setpoint**, set the required temperature using vertical sliding bar (I), then tap **Set**.




NOTE:

- Maximum 10 actions can be added.
- To remove an action, swipe it left on the action and then tap .

10. Enter the automation name (J).


You can choose the cover image that represents your automation by tapping .



11. Tap **Save**.

Once the automation is saved, it is visible on the **Automation** tab.

Using the  (K) you can enable and disable the automation.



Related Topics

- Using the device (Parent Topic)
- Example of an automation
- Editing an automation
- Deleting an automation

Example of an automation

This demonstration guides you through setting up an automation that activates heating to a set temperature of 20 °C when the room temperature drops below 18 °C.


NOTE: To ensure proper heating control, you must create two separate automations:

- Automation 1: Boost the heating when a presence is detected in the room.
- Automation 2: Turn off the heater when the room temperature reaches 25 °C or higher.


The room heater will not turn off automatically until you create another automation.

1. Go to **Automation** >  to create an automation.
2. To add a condition, tap **Add Condition** > **Device status change** > **Temperature/Humidity Sensor** > **Temperature**.

3. Set the temperature as 18 °C (A) and the condition as **less than** (B) and tap **Set**.




4. Read the information and tap **OK**.
5. To add an action, tap **Then > Add an action > Control a device > Heating > Setpoint**. Set the temperature to 20 °C (C), then tap **Set**.



6. Read the information and tap **OK**.
7. Enter the name of the automation.
TIP: You can choose the cover image that represents your automation by tapping .

8. Tap Save.
Once the automation is saved, it is visible on the **Automation** tab.




NOTE: You can enable or disable saved automations on the **Automations** tab by using  (D).

Related Topics

- Creating an automation (Parent Topic)

Editing an automation

1. On the **Home** screen, tap **Automations** .
2. Go to **Automation**, tap the automation you want to edit.
3. On the **Edit automation** screen, you can perform the following changes:
 - Change the icon .
 - Rename the automation.
 - Tap each condition to change the settings.
 - To remove a condition, slide the condition towards left and then tap  (A) to delete it.
 - Tap  **Add conditions** (B) to add new condition.
 - To change the order of actions, tap the **Then** option, and hold an action, then drag and drop to the desired position.



4. Tap **Save** to save the changes.


Related Topics

- Creating an automation (Parent Topic)

Deleting an automation

1. On the **Home** screen, tap **Automations** .
2. Go to **Automation**, tap the automation you want to delete.

- On the **Edit automation** screen, tap **Delete automation** (A) and read the confirmation message and then tap **OK** (B).



Related Topics


- Creating an automation (Parent Topic)

Removing the device

Using the Wiser Home app, you can remove the Thermostat from the Wiser system.

To delete the Thermostat:

- On the **Home** screen, tap .
- Tap **Devices > Radiator Thermostat > Delete** (A).




Related Topics

- ELKO - Smart Radiator Thermostat (Parent Topic)

Resetting the device

You can reset the Thermostat to factory default when it is attached to the radiator body. It can be reset manually at any time, e.g., when the Hub is replaced. To reset the Thermostat:

1. Twist and hold the cap in the “-” direction.
2. Wait for a few seconds until the center LED begins to flash red.
3. Hold the cap in the “-” direction until the LED flashes red 8 times.



4. Release the cap; all 3 LEDs flash once indicating a successful reset of the Thermostat.

Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)

Replacing the batteries

Replace the batteries of the device when the battery is low or critically low. The center LED of the radiator thermostat will signal when the batteries need to be replaced.

LED			
Left	Centre	Right	Meaning
Off	Solid Red, for 1s, once per hour.	Off	Battery, low. Replace
Off	Flashes Red, for 5s, once per minute.	Off	Batteries critically low. Replace immediately.

Replace the batteries with 2 x 1.5V IEC LR6 (AA) Alkaline batteries. Ensure the batteries ("+" and "-" ends) are correctly oriented. The polarity is indicated on the device's terminals.

NOTICE

USE ONLY STANDARD, NON-RECHARGEABLE AA ALKALINE BATTERIES

- **Do not use** rechargeable batteries, Zinc Carbon, or Zinc Chloride batteries.
- Rechargeable batteries are not optimized for Wiser device systems.

Failure to follow these instructions can result in equipment damage.

NOTE: Batteries should be disposed of according to statutory regulations. They must be recycled properly to protect the environment and reduce the waste of precious resources.



Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)

LED indications

Normal use

State	User Interaction	Left LED	Center LED	Right LED	Duration
Boost up	Twist the cap in the + direction				Solid for 5 seconds
Boost down	Twist the cap in the - direction				Solid for 5 seconds

Head calibration

State	User Interaction	Left LED	Center LED	Right LED	Duration
Start up	Insert the batteries				Single quick flash
Opening the valve	Automatic upon inserting batteries OR Twist and hold the cap in + direction for 8 seconds (for changing batteries)				Solid until the valve is open
Ready to install on the valve	The radiator thermostat is ready to install when the valve is fully open (see above)				Red and Blue: flash for up to 5 minutes
					Orange solid = not joined
					Green solid = joined
Closing the valve	Twist and hold the cap in the – direction for 2 seconds				Solid until the valve is closed
Joining	Twist and hold the cap in the + direction for 3 seconds				Pulses for up to 2 minutes
Joining success					Solid for 5 seconds
Joining failed	If no network is found after 2 minutes				Flashes for 5 seconds

Error state

State	User Interaction	Left LED	Center LED	Right LED	Duration
Low battery					Solid for 1 second (Repeated each hour)
Critical battery					Fast flash for 5 seconds (Repeated each minute)
No Signal	Twist the cap in the + direction to start a boost.				Fast flash for 5 seconds (Repeated)
No Signal	Twist the cap in the - direction to start a boost.				Fast flash for 5 seconds (Repeated)
No network	Twist the cap in the + or - direction to start a boost.				Solid with fade-out after 2 seconds. In this event, the radiator thermostat has not joined the wiser system and must either join the hub or be re-installed.

Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)

Troubleshooting

Symptom	Possible cause	Solution
The Thermostat is not responding or the app is not measuring the temperature.	Power failure or Wiser Hub generation restarted.	Post power failure, Wiser Hub generation needs up to 15 minutes to recover to normal.
The Thermostat displays offline in the app or the center LED blinks.	1. Poor signal between the Wiser hub and Thermostat. 2. The batteries need replacing in the Thermostat. 3. The Thermostat has been reset through the human interaction at physical device.	1. Rejoin the Thermostat in the app. 2. Replace the batteries and re-calibrate Thermostat, refer to the replacing the batteries, page 42 and calibrating the device, page 15 3. Re-configure the Thermostat.

Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)

Technical Data

Power supply	2 x 1.5 V IEC LR6 (AA) alkaline batteries or 2 x HR6 NiMH batteries
Without power supply:	Connection data are retained
Temperature setting range	5 °C - 30 °C
Temperature resolution	0.5 °C
Control accuracy	< 0.8 °C at 4 °C/h
Surface temperature at place of installation	max. 93 °C
Water temperature	max. 110 °C, max. continuous 73 °C
Ambient operating temperature	0 °C to 45 °C
Storage temperature	-20 °C to 65 °C
Operating frequency	2.4 GHz
Max. radio frequency power transmitted	max. 20 mW (13 dBm)
Degree of contamination	2
Radio range	30 m free field
Specification	Value
Energy class	IV - 2%
Software class	A
Protection rating	IP 30
Dimensions (HxØ)	93 x 51 mm

Related Topics

- [ELKO - Smart Radiator Thermostat \(Parent Topic\)](#)

Schneider Electric
35 rue Joseph Monier
92500 Rueil Malmaison
France

elko.no/contact
www.se.com

As standards, specifications, and design change from time to time, please ask for confirmation of the information given in this publication.

© 2025 – 2025 Schneider Electric. All rights reserved.

DUG_Smart Radiator Thermostat_WH-00