

ELKO - SmartBlinds Push

Wiser Home Device user guide

Information about features and functionality of the device.

10/2025



Legal Information

The information provided in this document contains general descriptions, technical characteristics and/or recommendations related to products/solutions.

This document is not intended as a substitute for a detailed study or operational and site-specific development or schematic plan. It is not to be used for determining suitability or reliability of the products/solutions for specific user applications. It is the duty of any such user to perform or have any professional expert of its choice (integrator, specifier or the like) perform the appropriate and comprehensive risk analysis, evaluation and testing of the products/solutions with respect to the relevant specific application or use thereof.

The Schneider Electric brand and any trademarks of Schneider Electric SE and its subsidiaries referred to in this document are the property of Schneider Electric SE or its subsidiaries. All other brands may be trademarks of their respective owner.

This document and its content are protected under applicable copyright laws and provided for informative use only. No part of this document may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Schneider Electric does not grant any right or license for commercial use of the document or its content, except for a non-exclusive and personal license to consult it on an "as is" basis.

Schneider Electric reserves the right to make changes or updates with respect to or in the content of this document or the format thereof, at any time without notice.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any errors or omissions in the informational content of this document, as well as any non-intended use or misuse of the content thereof.

Table of Contents

Safety Information.....	4
About the Document.....	5
ELKO SmartBlinds Push.....	8
About the device.....	8
Installing the device	9
Quick Home Connect.....	9
Blind Control Switches	9
Operating a Shades Control.....	11
Resetting the device in Quick Home Connect.....	11
LED Indications in Quick Home Connect.....	12
Troubleshooting in Quick Home Connect	12
Pairing the device with the Wiser Hub	12
Configuring the device	16
Selecting the device location.....	16
Renaming the device	17
Selecting device type	17
Setting the configure duration	18
Shutter Calibration	20
Seasonal Comfort Mode.....	23
Identifying the device	40
Removing the device from Wiser system	41
Resetting the device	41
Using the device.....	42
Operating the device manually.....	42
Opening/Closing the shutter using app	42
Setting up a schedule.....	44
Moments.....	46
Automation.....	52
LED Indication.....	58
Troubleshooting	59
Technical Data	59

Safety Information

Important Information

Read these instructions carefully and look at the equipment to become familiar with the device before trying to install, operate, service, or maintain it. The following special messages may appear throughout this manual or on the equipment to warn of potential hazards or to call attention to information that clarifies or simplifies a procedure.



The addition of either symbol to a “Danger” or “Warning” safety label indicates that an electrical hazard exists which will result in personal injury if the instructions are not followed.



This is the safety alert symbol. It is used to alert you to potential personal injury hazards. Obey all safety messages that accompany this symbol to avoid possible injury or death.

DANGER

DANGER indicates a hazardous situation which, if not avoided, **will result in** death or serious injury.

Failure to follow these instructions will result in death or serious injury.

WARNING

WARNING indicates a hazardous situation which, if not avoided, **could result in** death or serious injury.

CAUTION

CAUTION indicates a hazardous situation which, if not avoided, **could result in** minor or moderate injury.

NOTICE

NOTICE is used to address practices not related to physical injury.

About the Document

Document Scope

This document provides detailed guidance on the ELKO – SmartBlinds Push, covering its features, installation, pairing with the Wiser Hub, and configuration through the Wiser Home app. It explains how to set up device locations, rename and calibrate shutters, configure run times, and use advanced modes like Seasonal Comfort for automated climate control. Users are guided on manual and app-based operation, creating schedules, moments, and automations for personalized control, as well as troubleshooting and technical specifications. The document also describes integration with sensors and managing multiple devices for optimal home automation.

Validity Note

The characteristics of the products described in this document are intended to match the characteristics that are available on elko.no. As part of our corporate strategy for constant improvement, we may revise the content over time to enhance clarity and accuracy. If you see a difference between the characteristics in this document and the characteristics on elko.no, consider elko.no to contain the latest information.

For your safety

 DANGER
HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH Safe electrical installation must be carried out only by skilled professionals. Skilled professionals must prove profound knowledge in the following areas: - Connecting to installation networks. - Connecting several electrical devices. - Laying electric cables. - Safety standards, local wiring rules and regulations. Failure to follow these instructions will result in death or serious injury.

General Cybersecurity Information

In recent years, the growing number of networked machines and production plants has seen a corresponding increase in the potential for cyber threats, such as unauthorized access, data breaches, and operational disruptions. You must, therefore, consider all possible cybersecurity measures to help protect assets and systems against such threats.

To help keep your Schneider Electric products secure and protected, it is in your best interest to implement the cybersecurity best practices as described in the [Cybersecurity Best Practices](#) document.

Schneider Electric provides additional information and assistance:

- [Subscribe to the Schneider Electric security newsletter.](#)
- [Visit the Cybersecurity Support Portal web page to:](#)
 - [Find Security Notifications.](#)
 - [Report vulnerabilities and incidents.](#)
- [Visit the Schneider Electric Cybersecurity and Data Protection Posture web page to:](#)
 - [Access the cybersecurity posture.](#)
 - [Learn more about cybersecurity in the cybersecurity academy.](#)
 - [Explore the cybersecurity services from Schneider Electric.](#)

Environmental Data

Find and download comprehensive environmental data about your products, including RoHS compliance and REACH declarations as well as Product Environmental Profile (PEP), End-of-Life instructions (EOL) and much more.

<https://www.se.com/myschneider>



General information about Schneider Environmental Data Program

Click the link below to read about Schneider Electric's Environmental Data Program.

<https://www.se.com/ww/en/about-us/sustainability/environmental-data-program/>



Declaration of Conformity

Hereby, Schneider Electric Industries SAS, declares that this product is in compliance with the essential requirements and other relevant provisions of RADIO EQUIPMENT DIRECTIVE 2014/53/EU.

Declaration of conformity can be downloaded on:

- <https://go2se.com/ref=EKO09691>
- <https://go2se.com/ref=EKO09695>
- <https://go2se.com/ref=EKO09694>
- <https://go2se.com/ref=EKO09692>

Available Languages of the Document

The document is available in these languages:

- English
- Norwegian

Information on Non-Inclusive or Insensitive Terminology

As a responsible, inclusive company, Schneider Electric is constantly updating its communications and products that contain non-inclusive or insensitive terminology. However, despite these efforts, our content may still contain terms that are deemed inappropriate by some customers.

Trademarks


- Zigbee® is a registered trademark of the Connectivity Standards Alliance.
- Wiser™ is a trademark and the property of Schneider Electric, its subsidiaries and affiliated companies.
- QR Code is a registered trademark of DENSO WAVE INCORPORATED in Japan and other countries.

Other brands and registered trademarks are the property of their respective owners.

ELKO SmartBlinds Push



EKO09691



EKO09692, EKO09694, EKO09695

Related Topics

- About the device
- Installing the device
- Quick Home Connect
- Pairing the device with the Wiser Hub
- Configuring the device
- Removing the device from Wiser system
- Resetting the device
- Using the device
- LED Indication
- Troubleshooting
- Technical Data

About the device

You can use the ELKO Smart Blinds Push (hereinafter referred to as **blind control switch**) to control a blind or a roller shutter motor that is equipped with end position switches.

Control options

Home control using Wiser Home app: To control the blind control switch through the Wiser Home app you will need the **Wiser Hub**. Refer to *Pairing the device with the Wiser Hub*, page 12

Direct operation: The blind control switch can always be controlled directly on-site. You can also connect it with mechanical double push-buttons. Refer to *Manual operation*, page 42.

Related Topics

- [ELKO SmartBlinds Push \(Parent Topic\)](#)

Installing the device

Refer to the installation instruction supplied with this product.

See [Blind Control Switch](#).

Related Topics

- [ELKO SmartBlinds Push \(Parent Topic\)](#)

Quick Home Connect

Quick Home Connect is a wireless connectivity solution for Zigbee devices without the need for a Wiser Hub or smartphone application. Quick Home Connect is your starting point for wireless home automation. It performs functions like switching, dimming and shutter control using the Connected Wireless Switch (hereinafter referred to as Wireless switch) via a Zigbee network.

The **Wireless switch** is a battery-powered wireless push-button switch that is used to control Zigbee devices (such as dimmer, shutter, switch, and socket) within the same Zigbee network.

Limitations

- Quick Home Connect serves only as a room control solution.
- This solution does not support remote control, smartphone app usage, or scheduling features.


Related Topics

- [ELKO SmartBlinds Push \(Parent Topic\)](#)
- [Blind Control Switches](#)
- [Operating a Shades Control](#)
- [Resetting the device in Quick Home Connect](#)
- [LED Indications in Quick Home Connect](#)
- [Troubleshooting in Quick Home Connect](#)

Blind Control Switches


NOTE: To pair a Wireless switch with one blind control switch, follow the steps up to step 3. To continue with a second blind control switch, follow the next steps.

1. Remove the rocker from the Wireless switch.




2. Short press the top-right push button 5 times in quick succession on the Wireless switch.

The status LED blinks green.



3. Short press the first blind control switch 5 times in quick succession.

The status LED blinks green.




The shutter will move up and down a few times during the pairing process. The status LED stops blinking green on the Wireless switch, and the blind control switch indicates that the pairing is successful.

IMPORTANT: Check if the pairing was successful before you continue with the left channel.

4. Short press the top-left push button 5 times in quick succession on the Wireless switch.

The status LED blinks green.



5. Repeat step 3 on the second blind control switch.

The shutter will move up and down a few times during the pairing process. The status LED stops blinking green on the Wireless switch, and the blind control switch indicates that the pairing is successful.

6. Set up the shutter calibration manually.

Related Topics


- Quick Home Connect (Parent Topic)

Operating a Shades Control


You can operate the shades control using the Wireless switch.

Long press the top ($\wedge$) or bottom ($\vee$) of the Wiser Wireless switch ($> 0,5$ s) to move the shades control up or down.

- Press to open the shades control (A)
- Press to close the shades control (B)



- Short press the top ($\wedge$) or bottom ($\vee$) of the Wireless switch ($< 0,5$ s) to stop the moving shades control (C).
- Short press the top ($\wedge$) or bottom ($\vee$) of the Wireless switch ($< 0,5$ s) to adjust the slat position (D).



Related Topics

- Quick Home Connect (Parent Topic)

Resetting the device in Quick Home Connect

It is necessary to reset the devices in the following scenarios:

- Unpair the device in Quick Home Connect:
- Refer to
 - Resetting the Wireless switch
 - Resetting the device, page 41
- **Integrating into ELKO System**
 - If you wish to integrate the devices into Wiser Home System, reset all the devices in Quick Home Connect and refer to pairing the device with Wiser Hub.

Related Topics

- Quick Home Connect (Parent Topic)

LED Indications in Quick Home Connect

Pairing the device in Quick Home Connect

User Action	LED Indication	Status
Press the push button 5 times in quick succession.	LED blinks green, once per second. 	Pairing mode is active for 60 seconds. When pairing is completed, LED stops blinking. 

Related Topics

- Quick Home Connect (Parent Topic)

Troubleshooting in Quick Home Connect

Symptom	Possible cause	Solution
LED displays amber on the device.	Pairing not completed and returned to factory reset.	Pair the Wireless switch and the device again. Refer to • Blind Control Switches, page 12
Wireless switch not able to control the device reliably.	The Wireless switch and the device are too far away from each other.	Place the Wireless switch in a position closer to the device.
	The Wireless switch lost pairing	Pair the device again. Refer to • Blind Control Switches, page 12
	The Wireless switch battery is discharged.	Replace the battery of the Wireless switch

Scenario	Procedure
Control multiple devices with one Wireless switch.	To centralize control with one Wireless switch, first pair it with already connected devices. Then, pair the new device to existing group/network.
2-gang wireless switch with devices (smartrelay puck, smart blinds puck, multiwire puck dimmer, push-button dimmer, rotary dimmer, smart blinds push or smart socket).	Pair either left or right Wireless switch with any of the devices (smartrelay puck, smart blinds puck, multiwire puck dimmer, push-button dimmer, rotary dimmer, smart blinds push or smart socket). You can also pair another rocker of the Wireless switch with another device.

Related Topics

- Quick Home Connect (Parent Topic)

Pairing the device with the Wiser Hub


Using the Wiser Home app, pair your blind control switch with the **Wiser Hub** to access and control the blind control switch.

1. On the **Home** screen, tap .
2. Tap **Devices** >  > **Shutters** > **1-Gang Switch**.

TIP: You can also navigate by tapping **Control** >  > **Shutters** > **1-Gang Switch**.


3. Tap **Scan QR code** and allow the Wiser Home app to access your camera. Then, scan the QR code located on the device.

NOTE: If you are unable to find the correct QR code, tap **I can't find the correct QR code** to pair the device manually and proceed to step 4.




If the QR code is incorrect, a message **Incorrect QR code scanned** will appear. Tap **I can't scan the QR code** and choose one of the following options:


- **(A):** Enter the **Mac Address/EUI-64** and **Install Code**, then tap **Connect**. The app will verify if the Mac Address/EUI-64 and Install code are valid.
- **(B):** Tap this option if you are unable to find the Mac Address/EUI-64 and Install code.



4. Once the device is validated, tap **Next**, short-press the push button on the blind control switch 3 times and make sure that the LED blinks amber.



Wait for a few seconds until the LED turns green and the app confirms that the device is joined.



NOTE: If the LED is blinking green and red, see the instructions by tapping **LED blinking green and red?**.


5. Tap , enter a name of the device.
6. Tap **Next** and assign the device to a new room or an existing room and tap **Submit**.
7. Tap **Next** >  and select a **Device Type**:
 - **Shutter**: Proceed to step 8.
 - **Shutter with tilting slats**: Proceed to step 9 to 11.
8. Tap **Shutter** > **Next** and enter the open/close duration of shutter. Refer to *Setting default run time*, page 18.
9. Tap **Shutter with tilting slats** > **Slat Type**, select a slat type and tap **Set**:
 - Horizontal
 - Tilted
 - Vertical
10. Tap **Next** and enter the following durations:
 - a. **Open duration**: Time taken to open the shutter.
 - b. **Close duration**: Time taken to close the shutter.
 - c. **Tilt duration**: Time taken to rotate the slats completely from closed to open position.

Refer to *Setting default run time*, page 18.

11. Tap Submit.

After you pair the device, a success screen appears with the following options:

- **+ Add New Device:** Tap to continue pairing more devices.
- **Start Using Your Device:** Tap to start using the paired device.



NOTE: The success screen appears only if you are logged in as a **Home Owner**.

Once the pairing process is completed, the device name is listed on the **Control** tab under the **All** and **Room** tabs.

Related Topics

- ELKO SmartBlinds Push (Parent Topic)

Configuring the device


Selecting the device location

Using the Wiser Home app, you can add the blind control switch to any room (such as living room, bedroom, kitchen etc).

1. On the **Home** screen, tap .
2. Tap **Devices > Shutters > Blind control switch or Shutter slat > Location** (A) to assign the blind control switch to an existing room or a new room (B) and tap **Submit**.

NOTE:

- If the device is already assigned, you can remove it from the existing room by tapping **Remove from Room**.
- Blind control switch is the name given to the device when pairing with the **Wiser Hub**. You can assign a name according to your shutter type. Example, Shutter slat.




Related Topics

- Configuring the device (Parent Topic)

Renaming the device

You can rename the device using the Wiser Home app.

1. On the **Home** screen, tap .
2. Tap **Devices > Shutters > Blind control switch > Device Name** (A) to rename the device.



Related Topics


- Configuring the device (Parent Topic)

Selecting device type

Using the Wiser Home app, you can change the device type according to your need.

NOTE: The device type was selected as **Shutter** when pairing with the **Wiser Hub**. You can change the device type as **Shutter with tilting slats** if it has a tilt function.

1. On the Home screen, tap .
2. Tap **Devices > Shutters > Blind control switch**.
3. Tap  (A) and select a device type.
4. If the device type is selected as **Shutter with tilting slats**, tap  (B) and select a slat type (C).

5. Tap **Set**.

Related Topics

- Configuring the device (Parent Topic)

Setting the configure duration

Each shutter motor varies in the time it takes to complete the opening/closing movement (i.e., edge to edge). Therefore, the opening/closing time of the shutter must be determined in the app.

To determine the configured duration, manually open/close the shutter.

1. Record the time it takes to open/close the shutter completely.
2. Record the time it takes to rotate the slats completely from closed to open position for shutter with tilting slats.

Follow the procedure according to your shutter type:

- Shutter, page 18
- Shutter with tilting slats, page 20

Related Topics

- Configuring the device (Parent Topic)
- Shutter
- Shutter with tilting slats

Shutter

1. On the Home screen, tap .
2. Tap **Devices > Shutters > Blind control switch**.

3. Tap **Open duration/Close duration** (A) and enter the recorded shutter opening/closing time.

The screenshot shows the 'Device Details' screen for a '1 Gang switch'. The screen is divided into several sections: 'OPTIONS', 'ABOUT', and a bottom section with 'Identify' and 'Delete' buttons. The 'OPTIONS' section contains fields for 'Device Name' (Shutter), 'Location' (Living Room), 'Device Type' (Shutter), 'Open duration' (Max 5 Minutes, 01:30), and 'Close duration' (Max 5 Minutes, 01:30). The 'ABOUT' section contains 'Firmware Version' (Firmware 020519ff). The 'Open duration' and 'Close duration' fields are highlighted with a red box and labeled 'A'.

Device Details	
1 Gang switch	
Good Signal (-30dBm) ?	
OPTIONS ^	
Device Name	Shutter
Location	Living Room
Device Type	Shutter
Open duration	Max 5 Minutes 01:30
Close duration	Max 5 Minutes 01:30
ABOUT ^	
Firmware Version	
Firmware 020519ff	
Identify	
Delete	


Related Topics

- Setting the configure duration (Parent Topic)

Shutter with tilting slats

1. On the Home screen, tap .
2. Tap **Devices > Shutters > Shutter with tilting slats**.
3. Tap **Open duration/Close duration** (A) and enter the recorded shutter opening/closing time.
4. Tap (B) and enter the slat tilt duration according to the tilt position.

IMPORTANT: The minimum value to set the default time for Tilt duration is 01.00 s. If you set a value less than 01.00 s, it will not be saved.



Related Topics

- Setting the configure duration (Parent Topic)

Shutter Calibration

Related Topics

- Configuring the device (Parent Topic)
- Shutter calibration with Wiser app

Shutter calibration with Wiser app

The shutter motor is supplied in an uncalibrated state. Each shutter motor varies in the time it takes to complete the opening/closing movement (i.e., edge to edge).


IMPORTANT:

- It is necessary to select the device type and set the open/close duration before proceeding with shutter calibration. Refer to [Selecting device type](#), page 17 and [Setting configure duration](#), page 18.
- Do not use the shutter either manually or on the app during calibration to avoid interruption.
- Follow the procedure for shutter calibration according to the device type: **Shutter** or **Shutter with tilting slats**.

Shutter


1. After setting the open/close duration, go to the **Control** tab, and tap **All** devices or the room tab where the device is located.
2. On the device control screen, drag the sliding bar up/down to set the desired shutter opening percentage (A).

The shutter opens completely and then it reaches to the desired position set in step 2. The shutter is now calibrated.




Shutter with tilting slats

1. On the **Control** tab, tap **All** devices or the room tab where the device is located.
2. On the device control screen, in the **Position** tab, drag the sliding bar up/down to set the desired shutter opening percentage (A).



3. Tap **Slat Tilt**, drag the sliding bar up/down to set the desired shutter opening percentage (B) according to any one of the following tilt position:
- Horizontal
 - Tilted
 - Vertical



Related Topics

- Shutter Calibration (Parent Topic)

Seasonal Comfort Mode

The seasonal comfort mode uses the predicted temperature of a location or information from the light and temperature sensors to determine the temperature of a room and maintain a desired temperature in it by opening or closing the shutters.

It is a solution that efficiently maintains the desired temperature of a room in all seasons:

- Winter: In winters, the shutters stay open during days and close after sunset. This uses the maximum natural heat to maintain the desired room temperature.
- Summer: In time summers, the shutters close during the day such that the desired temperature is maintained in a room while allowing a good level of light inside the room.
- Mid-seasons: In seasons other than summer or winter:
 - If the highest temperature of a day reaches 22° C or above, the seasonal comfort mode operates the shutters the same as in summers.
 - If the highest temperature of a day is below 22° C, the seasonal comfort mode operates the shutters the same as in winters.

The Seasonal Comfort Mode adapts its operation based on the devices available in your system, offering three levels of algorithm efficiency. Each level improves the comfort and energy savings by integrating additional data sources:

- Basic level - Control based on time & geographical location:

At this level, it uses your home's geographical location and the time of day to manage shutters automatically based on the estimated sunrise and sunset times. This maintains the optimum light and temperature at home. This level is ideal for users who want a simple, automated solution without additional sensors.
- Enhanced Level - Temperature - Driven Optimization:

At this level, it uses the local indoor and outdoor temperature in addition to the time and your home's geographical location. It manages the shutters dynamically based on the real-time temperature conditions to improve comfort.
- Advanced Level - Best-in-class optimization with light sensors:

At this level, it further improves the shutter management by using the real-time light intensity measured by the outdoor motion sensors and the indoor and outdoor temperature.

It offers maximum efficiency by adapting shutter movements based on actual temperature and natural light, rather than relying only on the estimated sunrise/sunset times.

TIP: Choosing the right level for shutter operation:

The Seasonal Comfort Mode adapts to the devices installed in your system. Even if you don't have all the required sensors, you can still benefit from the feature at a basic level. This flexible approach ensures that you can experience optimized comfort and energy efficiency, regardless of your system setup.

However, for the best results, we recommend using the full set of compatible devices.

NOTE: The seasonal comfort mode performs accurately when the indoor and outdoor temperature sensors (Temperature/Humidity Sensor) and outdoor motion sensors are installed at home.

IMPORTANT: The IP rating of the sensors used for the seasonal comfort mode are as follows:

Sensors	IP rating
Outdoor Motion Sensor	IP66 - Sensor is protected against dust and water ingress.
Temperature/Humidity Sensor	IP20 - Sensor is protected against solid objects of size more than 12mm.

Therefore, they should be installed at a suitable location at home.

Related Topics

- Configuring the device (Parent Topic)

Configuring the seasonal comfort mode


Using the Wiser Home app, you can configure the seasonal comfort mode to define the desired temperature and location of the shutters and sensors in the home.

Pre-requisite:

- Shutters must be installed at home.
- Add your address to the account. Tap  > **Account > My Home**.
- Calibrate your shutters. Refer to [Shutter calibration](#), page 20 or [Shutter calibration with tilting slats](#), page 20 based on the shutter type.
- The Outdoor Motion Sensor detects light and external temperature.
- Make sure that the Outdoor Motion Sensor is facing towards the floor and not facing the sun.


To configure the seasonal comfort mode:

- On the **Home** screen, tap  > **Smart Modes > Seasonal Comfort Mode**.




Details about the seasonal comfort mode are displayed.


2. Swipe left to see the additional details and tap **Next > Continue** to start configuring the seasonal comfort mode.



3. Define the orientation in which the shutters are installed at home:
 - a. Select the orientation in which each shutter is installed at home and tap **Next**.



- b. If any shutter is covering a door, tap **Yes I have shutters over a door**.
TIP: If no shutter is covering a door or you have an alternative way to enter your home, tap **No, next step** and continue with step 4. In this case, the seasonal comfort mode close the shutters fully while you're outside.
 - c. Select the shutters covering the doors from the list (A) and then tap **Next**.



The selected shutters will close up to 50% in order to make sure that you do not get locked out when doors are covered by shutters.

4. Set the desired inside and outside discomfort temperatures and then tap **Next**.

< Seasonal Comfort Mode ⓘ

Step 2 of 3

Please choose Your discomfort temperatures.

INDOOR DISCOMFORT TEMPERATURE

24°

25°

26°

OUTSIDE DISCOMFORT TEMPERATURE

26°

27°

28°

Next



NOTE: Discomfort temperature refers to a temperatures above which an individual feels uncomfortable. When the ambient temperature raises above the set inside and outside discomfort temperatures, the seasonal comfort mode closes the shutters to maintain the indoor temperature. Maintaining a comfortable indoor temperature helps improve well-being and productivity.

- 5. Select the orientation in which the light sensors and the outside temperature sensors are installed at home:
 - a. Select the orientation in which the light sensors are installed and tap **Next**.



NOTE: If the light sensors are not installed, this page will not appear.

- b. Tap **Yes** to select the orientation of the outside temperature sensors.



NOTE: You can tap **No** if the outside temperature sensors are not installed.

6. Tap **Next** to define the time when the seasonal comfort mode will **BEGIN AT** and the time when it will **FINISH AT**.

Seasonal Comfort Mode ⓘ

Step 3 of 3



Please select when you would like your seasonal comfort mode to begin and finish.

BEGIN AT

-10 minutes

Sunrise

+10 minutes

FINISH AT

-10 minutes

Sunset

+10 minutes

Next

NOTE: You can start and stop the seasonal comfort mode some time before or after the sunrise/sunset.

This improves the accuracy of the settings when light sensors are not installed and your building is blocked by another building or a mountain that obstructs the sunlight from reaching your location.

7. Tap **Next**.

If all the rooms in the home have temperature sensors, configuration of the seasonal comfort mode is done.

8. If shutters are available in rooms without temperature sensors, you can control those shutters as follows:

NOTE: Wiser Home app displays the rooms without temperature sensors in list (B).

Seasonal Comfort Mode

We have noticed you have shutters setup in rooms that do not have a temperature sensor or thermostat.

To be able to close these shutters, you can choose another room's temperature.

You can also choose not to set this and we will close the shutters in these rooms based on the outside temperature and light levels.

- Bedroom 1
- Bedroom 2
- Kitchen

Next

- Select a room from the list (B) and tap **Next**.
 - You can use one of the following as a reference temperature for the selected room:
 - Temperature detected by temperature sensor of another room.
 - Average temperature detected by all the temperature sensors at home.
- A. To use the temperature of another room as the reference temperature:
- Select a room from the list (C).

NOTE: The temperature of the selected room will be considered as the reference temperature.

Seasonal Comfort Mode

Which other room in your home would you like to use to record the temperature for <Room Name>?

- Living Room
- Bedroom
- Kitchen

Use average home temp

- Go back to the previous page and tap **Next** to complete the setup.

< **Seasonal Comfort Mode**

We have noticed you have shutters setup in rooms that do not have a temperature sensor or thermostat.

To be able to close these shutters, you can choose another room's temperature.

You can also choose not to set this and we will close the shutters in these rooms based on the outside temperature and light levels.

Bedroom 1
Using temperature from the <Room Name> 

Bedroom 2
Using average home temperature 

Kitchen 

Next

B. To use the average temperature detected by all the temperature sensors as the reference temperature:

1. Tap **Use average home temp** (D).

< **Seasonal Comfort Mode**

Which other room in your home would you like to use to record the temperature for <Room Name>?

Living Room 

Bedroom 

Kitchen 

Use average home temp 

2. Tap **Yes, i'm sure** to complete the setup.

c. Tap **Done** to see the updated configuration.

Seasonal Comfort Mode



You're all good to go..

Seasonal comfort mode will now adjust your shutters to optimise heating and cooling in your home based on:

- ✓ The seasons of the year
- ✓ The brightness outside your home
- ✓ The time of day
- ✓ The temperature in and outside your home

You can come back here anytime to change these settings.

Done

< **Seasonal Comfort Mode** 

Seasonal Comfort Mode 

Shutters
3 active 

Temperature
Indoor 25°, Outdoor 27° 

Time
Sunrise +10, Sunset -10 

Light (LUX) sensors
2 active 

Outside temp sensors
2 active 

Other room sensors
3 active 

Seasonal comfort mode has been successfully configured. Your supported devices will now be adjusted to optimize heating and cooling in your home.

Setting the seasonal comfort mode


Using the Wiser Home app, you can change the configuration of the seasonal comfort mode.

Pre-requisite:

- Calibrate your shutters. Refer to Shutter calibration, page 20 or Shutter calibration with titling slats, page 20 based on the shutter type.

On the **Home** screen, tap  > **Smart Modes** > **Seasonal Comfort Mode**.

The **Seasonal Comfort Mode** set-up page is displayed, where you can update the following configurations:



To change the configuration of the seasonal comfort mode:

A	Seasonal Comfort Mode: Tap the toggle switch to turn the seasonal comfort mode ON/ OFF.
B	Shutters: Tap to change the orientation and location of the shutters in the Wiser Home app. Refer to Changing the shutter orientation and location, page 33 for more details.
C	Temperature: Tap to change the threshold inside and outside temperatures in the Wiser Home app. Refer to Setting the threshold temperature, page 34 for more details.
D	Time: Tap to change the start and end time of the seasonal comfort mode in the Wiser Home app. Refer to Setting the start and end time, page 34 for more details.
E	Light (LUX) sensors: Tap to change the orientation of the light sensors in the Wiser Home app. Refer to Changing the orientation of the light sensors, page 35 for more details.
F	Outside temp sensors: Tap to change the orientation of the outside temperature sensors in the Wiser Home app. Refer to Changing the orientation of the outside temperature sensors, page 36 for more details.
G	Other room sensors: Tap to manage the shutter operation without temperature sensors. Refer to Managing the shutter operation without temperature sensor, page 37 for more details.

Related Topics


- Changing the shutter orientation and location
- Setting the threshold temperature
- Setting the start and end time
- Changing the orientation of light sensors
- Changing the orientation of outside temperature sensors
- Managing shutter operation without temperature sensor

Changing the shutter orientation and location

You can change the orientation and location of the shutter in Wiser Home app.

To change the orientation and location of the shutters:


1. In the **Seasonal Comfort Mode** set-up page, tap **Shutters**.
2. Update the orientation of the shutters and tap **Set**.



3. If any shutter is covering a door, tap **Yes I have shutters over a door** to define its location.

NOTE: If no shutters cover a door, tap **No**.

4. Select the shutters covering the doors from the list (A) and tap **Finish**.



Related Topics

- Setting the seasonal comfort mode (Parent Topic)

Setting the threshold temperature

Using the Wiser Home app, you can define the inside and outside temperature of a room above which the shutters shall close.

To set the threshold inside and outside temperature:

1. In the **Seasonal Comfort Mode** set-up page, tap **Temperature**.

2. Set the inside and outside desired temperatures and tap **Set**.

Related Topics

- Setting the seasonal comfort mode (Parent Topic)

Setting the start and end time

Using the Wiser Home app, you can define the start and end time of the seasonal comfort mode.

To set the start and end time of the seasonal comfort mode:

1. In the **Seasonal Comfort Mode** set-up page, tap **Time**.

2. Select the time when the seasonal comfort mode will **BEGIN AT** and the time when it will **FINISH AT**.

NOTE: You can start and stop the seasonal comfort mode some time before or after the sunrise/sunset.

3. Tap **Set**.

Related Topics

- Setting the seasonal comfort mode (Parent Topic)


Changing the orientation of light sensors

You can change the orientation of the light sensors in the Wiser Home app.

To change the orientation of the light sensors:

1. In the **Seasonal Comfort Mode** set-up page, tap **Light (LUX) sensors**.
2. Tap  to see the available light sensors in Wiser Home app.

3. Select the orientation in which the light sensors are facing and tap **Set**.



Related Topics


- Setting the seasonal comfort mode (Parent Topic)

Changing the orientation of outside temperature sensors


You can change the orientation of the outside temperature sensors in the Wiser Home app.

To change the orientation of the outside temperature sensors:

1. In the **Seasonal Comfort Mode** set-up page, tap **Outside temp sensors**.
2. Tap  to see the available outside temperature sensors in Wiser Home app.



3. Select the orientation in which the outside temperature sensors are facing and tap **Set**.



Related Topics

- Setting the seasonal comfort mode (Parent Topic)


Managing shutter operation without temperature sensor

Using the Wiser Home app, you can manage the shutter operation of a room where no temperature sensor is installed.

To define the reference temperature:

1. In the **Seasonal Comfort Mode** set-up page, tap **Other room sensors**.


NOTE: Wiser Home app displays the rooms without temperature sensors in list (A).




2. Select a room from the list (A).

3. You can use one of the following temperatures as a reference temperature for the selected room:
 - Temperature detected by temperature sensor of another room.
 - Average temperature detected by all the temperature sensors at home.
- A. To use the temperature of another room as the reference temperature select a room from the list (B).

NOTE: The temperature of the selected room will be considered as the reference temperature.



- B. To use the average temperature detected by all the temperature sensors as the reference temperature:
 1. Tap **Use average home temp** (C).



2. Tap **Yes, i'm sure**.

Related Topics

- Setting the seasonal comfort mode (Parent Topic)


Pausing the seasonal comfort mode

Using the Wiser Home app, you can set the shutter position and pause the seasonal comfort mode for some time.



To pause the seasonal comfort mode:

1. On the **Control** tab, select the shutter for which you want to pause the seasonal comfort mode.

TIP: Tap up/down button (A) to move the shutter to required position.



2. Tap the pause button to select the time for which you want to pause the seasonal comfort mode.




TIP: You can tap **Cancel** at any time to stop the pause.

IMPORTANT: If you manually override the shutter, the system will pause for 1 hour from the time of the first manual adjustment. However, we recommend to pause the seasonal comfort mode using the Wiser Home app.

Identifying the device

Using the Wiser Home app, identify the blind control switch among the devices available in a home.

1. On the **Home** screen, tap .
2. Tap **Devices > Shutters > Blind control switch** or **Shutter slat > Identify (A)**.



The status LED blinks red and the shutter opens/closes gradually, upon successful identification of the blind control switch or shutter slat.

3. Tap **OK** to finish identifying the device.


Related Topics

- Configuring the device (Parent Topic)

Removing the device from Wiser system

Using the Wiser app, you can remove the blind control switch from the system.
To remove the device:

1. On the **Home** screen, tap .
2. Tap **Devices > Shutters > Blind control switch** or **Shutter slat > Delete (A)**.



NOTE:

- Removing the device will reset the blind control switch. The LED starts blinking amber indicating that the blind control switch is ready for pairing.
- If there is a problem while pairing or resetting the blind control switch, refer to [Resetting the device](#), page 41.

Related Topics

- [ELKO SmartBlinds Push \(Parent Topic\)](#)

Resetting the device


You can reset the device to factory default manually.

Short-press the push button 3 times (<0.5 s) and then long-press the push button once (>10 s).

The LED blinks red after 10 s, and then release the push button.

Upon successful reset, the LED stops blinking. Then, the device restarts and blinks green for a few seconds.

NOTE: After reset, the LED turns amber indicating that it is ready for pairing.



Related Topics

- ELKO SmartBlinds Push (Parent Topic)


Using the device

Related Topics

- ELKO SmartBlinds Push (Parent Topic)
- Operating the device manually
- Opening/Closing the shutter using app
- Setting up a schedule
- Moments
- Automation

Operating the device manually

- Long press the blind control switch ($> 0,5$ s) to move the shutter up or down (A).
 - Press (Λ) to open the shutter.
 - Press (v) to close the shutter.
- Short press ($< 0,5$ s) to stop the moving shutter (B).
- **For shutter with tilting slats:** When the shutter is not moving short press ($< 0,5$ s) the blind control switch to adjust the slat position (C).



Related Topics


- Using the device (Parent Topic)

Opening/Closing the shutter using app

To open/close the shutter:

1. On the **Control** tab, tap **All** devices or the room tab where the device is located.

2. Tap   (A) or (B) of the shutter or shutter slat to open/close it.



TIP: You can also open/close the shutter or shutter slat:

- By selecting of the shutter or shutter slat and using the slider in the device control screen to open/close it.
- When you add it to your **Favourites**. To know more about **Favourite**, refer to **Managing Favourite** in the respective System User Guide.

NOTE: If you only have a single device in the Wiser System, the **Control** tab will not be visible. All functions will be accessible through the **Home** screen.

Related Topics


- Using the device (Parent Topic)

Setting up a schedule

The shutter can be controlled and triggered by a schedule. Once the schedule is set, your system will follow the active schedule. You can create or modify the schedules at any time. The devices can be fully controlled by schedule. Once the schedule is set, the devices operates at a given time.


To create a schedule:

1. On the **Home** screen, tap  > **Schedules** > .
2. Enter a name of the schedule (A).
3. Select a device type (B).
4. Select the list of devices (C) to which the schedule must apply.
5. Tap **Create**.



6. Tap  to add an event.

7. Select a state (Open/Closed/percentage) (D), time period (E) and tap **Set**.



TIP:

- You can add multiple schedules based on your requirement. Select days, tap , set on/off state and time.
- You can copy the existing schedule to another schedule or to the days of your choice. Tap .
 - Tap **Schedule** and select an existing schedule and tap **Copy**.
 - Tap **Day** and select the days you want to assign and tap **Copy**.
 - When the schedule begins, you can see the until time on the **Control** tab under the device name.
- On the top-right screen, tap  and select **Follow Schedule** toggle switch to turn On/Off the schedule.
- When the schedule begins, you can see the **until time** in the following screens:
 - Device Control Screen.
 - Control tab under the device name.
 - Favourite devices section on the home screen.

Related Topics

- Using the device (Parent Topic)

Moments

Moment allows you to group multiple actions that are usually performed together. By using the Wiser Home app, you can create moments based on your needs.

Related Topics


- Using the device (Parent Topic)
- Creating a moment
- Editing a moment
- Deleting a moment

Creating a moment


1. On the **Home** screen, tap .
2. Go to **Moments** and then tap  to create a moment.
3. Enter the name of the moment (A).

TIP: You can choose the cover image that represents your moment by tapping .

4. Tap **Add actions** (B) to select the list of devices.




5. Select the devices (C) you want to set an action and tap **Done**.



6. On the **Moment creator** page, select any one of the following device and set actions.


– **For shutter:**

- Drag the sliding bar up/down to open/close the shutter completely (D, E).
- Drag the sliding bar to keep the shutter in the preferred position.



– **For Shutter slat:**

- Select **Position** (F) and drag the sliding bar up/down to open/close the shutter (G).
- Select **Slat Tilt** (F) and drag the sliding bar up/down to adjust the tilt position of the shutter (H).



7. Tap **Set**.
8. Once all conditions are set, tap **Save**.

Once the moment is saved, it is visible on the **Moments** tab. You can tap on the moment to enable it.

TIP:

- If you want to see the created moments on the **Home** screen, go to **Home** >  > **Home Screen** > **Moments** and enable the **Moments** toggle switch.
- You can also rearrange the moments by tapping **Edit** from the **Moments** tab on the **Home** screen, or by tapping **Automation** > **Moments** > **Reorder**.


Related Topics

- Moments (Parent Topic)

Editing a moment

To edit a moment:

1. On the **Home** screen, tap .
2. Go to **Moments**, locate the moment you want to edit and tap .
3. On the **Moment Editor** page, you can perform following changes:
 - Change the icon .
 - Rename the moment.
 - Tap each action to change the settings.
 - To remove an action, slide the action to the left and then tap  (A) to delete it.
 - Tap  **Add actions** (B) to add new action.



4. Tap **Save** to save the changes.

Related Topics


- Moments (Parent Topic)

Deleting a moment

To delete a moment:

1. On the **Home** screen, tap .
2. Go to **Moments**, locate the moment you want to delete and tap  (A).

- On the Moment Editor page, tap **Delete** (A) and tap **OK** (B).



Related Topics

- Moments (Parent Topic)

Automation

An automation allows you to trigger an action automatically or at scheduled times when certain conditions are met. By using the Wiser Home app, you can create automations based on your needs. This example demonstrates how a device works when the condition is met.

Related Topics


- Using the device (Parent Topic)
- Creating an automation
- Editing an automation
- Deleting an automation

Creating an automation

Follow the steps to create an automation:

1. On the **Home** screen, tap .
2. Go to **Automation** and then tap  to create an automation.
3. Enter the name of the automation (A) and select any of the following conditions to trigger an automation.
 - **All conditions:** All conditions must be met to trigger an automation.
 - **Any condition:** Any one of the condition must be met to trigger an automation.


TIP: You can choose the cover image that represents your automation by tapping .




4. Tap **Add conditions** (B) and select any of the following (C).

- **Device status change** (Select the device): An automation will be triggered based on a device status, such as the opening of a shutter or the detection of movement by a motion sensor.
- **Away Mode** (Enable or Disable): Away mode can also trigger an automation to turn on the lights, close the shutter etc. For more information about **Away Mode**, refer to the system user guide.

NOTE: Maximum 10 conditions can be added.



- a. In this example, we will select **Device status change** and choose a device to set the condition. Then, we will select the state of the device that will trigger the automation, such as the ON state of a relay switch.





- b. After selecting the device, tap **Set** on the top-right screen.

TIP: If you want to change the condition, swipe it to the left and tap the bin icon. Then add a new condition with the required parameters.

5. To start your automation at a particular time, tap **When > Add time** and select any of the following (D):

NOTE: Maximum 10 time entries can be added.


- **Specific time of day** - The automation will trigger at a specific time of the day, such as at sunrise, sunset, or at 8:00 AM.
- **Period of time** - The automation will be trigger during time periods such as from sunrise to sunset, or sunset to sunrise, or from 8:00 AM to 5:00 PM.



6. To add an action, tap **Then > Add an action** and select any of the following (E):


NOTE: Maximum 10 actions can be added.

- **Control a device** - Select the device and set the desired state of the device.
- **Send notification** - You will be notified if the condition is met.
- **Activate a moment** - Select a Moment to activate during the automation.
- **Wait** - This option allows you to add a delay in an automation sequence. You can set the wait time in increments of 1 hour and 1 minute, up to a maximum of 24 hours. This feature is useful for delaying actions within an automation.




- a. In this example, we will initially select **Control a device** and select **Shutter** (F) as the device to trigger an action, later, we will select for the **Wait** option to add a delay in the automation.


IMPORTANT: You cannot select the same device that you selected for **Add conditions** in Step 4. The device should be different.



- b. Set the state, such as the Open or Closed state of the Shutter. Then, tap **Set** located on the top-right screen.




- c. Again, tap **Add an action** and select **Wait** option.
- d. Scroll through the minutes and set the wait time to 1 minute. Then, tap **Set** located on the top-right screen.



7. Tap **Save**.

The saved Automation is displayed on the **Automation** page. Tap the toggle switch (G) on the Automation page to enable/disable the Automation.




Related Topics

- Automation (Parent Topic)


Editing an automation

Follow the steps to edit an automation:

1. On the **Home** screen, tap .
2. Go to **Automation**, tap the automation you want to edit (A).



3. On the **Edit automation** page, you can:
 - Change the icon.
 - Rename the automation.
 - Change the condition or action.
4. Remove the Condition or Action by swiping it to the left and tapping the **bin** icon (B).



5. Add a new condition or action and then tap **Save**.


Related Topics

- Automation (Parent Topic)

Deleting an automation

Follow the steps to delete an automation:

1. On the **Home** screen, tap .
2. Go to **Automation**, you want to delete and tap .
3. On the Edit automation page, tap **Delete Automation** (A) and read the confirmation message and then tap **Ok** (B).



Related Topics

- Automation (Parent Topic)

LED Indication

Pairing

User Action	LED Indication	Status
Press the push button 3 times	LED blinks amber per second. 	Pairing mode is active for 30 seconds. When pairing is completed, LED glows green for some time before turning off. 

Resetting

User Action	LED Indication	Status
Press the push button 3 times and hold it down once for > 10 s.	After 10 s, the LED blinks red. 	The device is in reset mode. It is reset to the factory settings after 10 seconds. The device then restarts and the LED blinks green for a few seconds and then stays amber. 

Related Topics

- [ELKO SmartBlinds Push \(Parent Topic\)](#)

Troubleshooting

Symptom	Solution
Connected blinds cannot be controlled.	• Check power supply. • Remove power to the blinds control switch and then re-connect power again. • Check the load. • In the case of an external push button, check the wiring. • Re-couple devices.
Blinds is not driving to the desired position.	Reset to factory default settings, refer to Resetting the device , page 41

Related Topics

- [ELKO SmartBlinds Push \(Parent Topic\)](#)

Technical Data

Nominal voltage	AC 230 V, 50 Hz		
Nominal power	Load type	Load name	Load value
		Motor	500 W
Standby	Maximum 0.4 W		
Connecting Terminals	Screw terminals for max. 2 x 2.5 mm², 0.5 Nm		
Extension unit	Mechanical Double push-buttons, unlimited number, max. 50 m		
Fuse protection	10 A circuit breaker		
Nominal current	4 A, $\cos\varphi = 0.6$		
Frequency band	2.4 GHz		
Transmission capacity	2.5 mW		
Communication protocol	Zigbee 3.0 certified		

Related Topics

- [ELKO SmartBlinds Push \(Parent Topic\)](#)

Schneider Electric
35 rue Joseph Monier
92500 Rueil Malmaison
France

elko.no/contact
www.se.com

As standards, specifications, and design change from time to time, please ask for confirmation of the information given in this publication.

© 2025 – 2025 Schneider Electric. All rights reserved.

DUG_SmartBlinds Push_WH-00