

# Unica - Connected Universal Push-button Dimmer LED

## Device user guide

Information about features and functionality of the devices  
02/2024

**IMPORTANT:** Select your system to access the right user guide

If you have  
**Wiser Gateway**  
(CCT501901) and  
**Wiser app**, continue  
reading this  
device user guide.

### Wiser by SE System


WiFer

Schneider  
Electric

Wiser app



CCT501901  
Wiser Gateway


If you have  
**Wiser Hub/HubR**  
2nd Generation  
(CCT501801 or  
CCTFR6311G2) and  
**Wiser Home app**, then  
click here 

### Wiser Home System

WiFer

Schneider  
Electric

Wiser Home app



CCT501801  
Wiser Hub  
2<sup>nd</sup> Generation



CCTFR6311G2  
Wiser HubR  
2<sup>nd</sup> Generation

# Legal Information

The information provided in this document contains general descriptions, technical characteristics and/or recommendations related to products/solutions.

This document is not intended as a substitute for a detailed study or operational and site-specific development or schematic plan. It is not to be used for determining suitability or reliability of the products/solutions for specific user applications. It is the duty of any such user to perform or have any professional expert of its choice (integrator, specifier or the like) perform the appropriate and comprehensive risk analysis, evaluation and testing of the products/solutions with respect to the relevant specific application or use thereof.

The Schneider Electric brand and any trademarks of Schneider Electric SE and its subsidiaries referred to in this document are the property of Schneider Electric SE or its subsidiaries. All other brands may be trademarks of their respective owner.

This document and its content are protected under applicable copyright laws and provided for informative use only. No part of this document may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Schneider Electric does not grant any right or license for commercial use of the document or its content, except for a non-exclusive and personal license to consult it on an "as is" basis.

Schneider Electric reserves the right to make changes or updates with respect to or in the content of this document or the format thereof, at any time without notice.

**To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any errors or omissions in the informational content of this document, as well as any non-intended use or misuse of the content thereof.**

---

# Table of Contents

|  |    |
|--|----|
| Safety information .....                                 | 4  |
| Unica - Connected Universal Push-button Dimmer LED ..... | 5  |
| For your safety .....                                    | 5  |
| About the device .....                                   | 6  |
| Installing the device .....                              | 6  |
| Pairing the device .....                                 | 6  |
| Pairing device manually .....                            | 7  |
| Pairing device with auto scan .....                      | 8  |
| Configuring the device .....                             | 9  |
| Changing the device icon .....                           | 9  |
| Renaming the device .....                                | 10 |
| Changing the device location .....                       | 10 |
| Removing the device .....                                | 11 |
| Resetting the device .....                               | 11 |
| Using the device .....                                   | 12 |
| Switching/Dimming the device manually .....              | 12 |
| Switching/Dimming the device using app .....             | 13 |
| Creating a schedule .....                                | 14 |
| Dimmer settings .....                                    | 15 |
| Creating a moment .....                                  | 19 |
| Creating an automation .....                             | 21 |
| LED Indication .....                                     | 26 |
| Troubleshooting .....                                    | 26 |
| Technical Data .....                                     | 27 |

# Safety information

## Important information

Read these instructions carefully and look at the equipment to become familiar with the device before trying to install, operate, service, or maintain it. The following special messages may appear throughout this manual or on the equipment to warn of potential hazards or to call attention to information that clarifies or simplifies a procedure.



The addition of either symbol to a “Danger” or “Warning” safety label indicates that an electrical hazard exists which will result in personal injury if the instructions are not followed.



This is the safety alert symbol. It is used to alert you to potential personal injury hazards. Obey all safety messages that accompany this symbol to avoid possible injury or death.

### **DANGER**

**DANGER** indicates a hazardous situation which, if not avoided, **will result in** death or serious injury.

**Failure to follow these instructions will result in death or serious injury.**

### **WARNING**

**WARNING** indicates a hazardous situation which, if not avoided, **could result in** death or serious injury.

### **CAUTION**


**CAUTION** indicates a hazardous situation which, if not avoided, **could result in** minor or moderate injury.

### **NOTICE**

NOTICE is used to address practices not related to physical injury.



# Unica - Connected Universal Push-button Dimmer LED



NU5517xx



NU3517xx

## For your safety

### **⚠ DANGER**

#### **HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH**

Safe electrical installation must be carried out only by skilled professionals. Skilled professionals must prove profound knowledge in the following areas:

- Connecting to installation networks.
- Connecting several electrical devices.
- Laying electric cables.
- Safety standards, local wiring rules and regulations.

**Failure to follow these instructions will result in death or serious injury.**

**⚠ DANGER****RISK OF FATAL INJURY FROM ELECTRIC SHOCK**

The output may carry electric current even when the load is switched Off.

Disconnect the device from the supply by means of the fuse in the incoming circuit before working on the device.

**Failure to follow these instructions will result in death or serious injury.**

**⚠ CAUTION****THE DEVICE MAY BE DAMAGED**

Only connect dimmable load.

**Failure to follow these instructions can result in injury or equipment damage.**

## About the device

The Connected Universal Push Button Dimmer LED (hereinafter referred to as **Dimmerdimmer**) is a push button device that can be used to switch and dim LED, ohmic, inductive or capacitive loads manually or remotely.

## Control options

**Home control:** To control the dimmer through the Wiser app you will need the Wiser Gateway **Wiser Hub**.

**Direct operation:** The dimmer can always be controlled directly on-site. You can also connect any number of mechanical push buttons.

## Functions

- The device can detect the load automatically.
- It provides thermal protection, overload-resistance and short-circuit protection.

## Installing the device

Refer to the installation instruction supplied with this product.


See Connected Universal Push Button Dimmer LED.


## Pairing the device

Using the Wiser app, pair your device with the **Gateway/Hub** to access and control the device. You can either add the device manually or do an auto-scan to pair it.

## Pairing device manually

To pair the device manually:


1. On **Home** page, tap **+**.
2. Tap  and select the required **Wiser Hub** on the slide-up menu.
3. Select an option to add the device (A):
  - **Add Device with Install Code**
  - **Add Device without Install Code**



**TIP:** It is highly recommended to add the device with install code.


4. To pair the device with install code, tap **Add Device with Install Code** to display the slide-up menu. Select any one of the options (B):
  - **Scan Install Code** - you can scan the device for the install code
  - **Enter Install Code Manually** - you can manually enter the install code from the device

After pairing the device with install code, proceed to **Step 6**.




5. To pair the device without install code, tap **Add Device without Install Code**.

6. Short press upper part of the push-button 3 times ( $< 0,5$  s).




The LED blinks amber.

7. In the app, select **Confirm LED is blinking amber** and tap **Start configuration (C)**.



8. After a few seconds, a solid green LED indicates that the device is successfully paired to the Gateway/Hub.



9. Once the device is added in the app, tap **Done**.

## Pairing device with auto scan

Pairing the device with auto scan automatically discovers the device when the corresponding device is powered on.  
To pair the device with auto scan:

1. On the **Home** page, tap **+**.
2. Tap **Auto scan** and then tap **Confirm**.
3. If you have multiple hubs, do Step 4 or proceed to Step 5.
4. Tap **Select hub** and select the Wiser hub from the slide-up menu.


5. Short press upper part of the push button 3 times (< 0,5 s).

**NOTE:**

- The LED blinks amber.
- Wait for a few seconds until the device search is complete.

**TIP:** If you want to pair multiple devices at once, perform step 5 on each device and wait for a few seconds for them to be detected.

6. Tap **Next** (A) and select **Push Button Dimmer**.





7. Once the device is added successfully, tap **Done**.


## Configuring the device

### Changing the device icon

You can change the device icon using the Wisir app.



1. On the Home page, select and tap the device you wish to change the icon.
2. At the top right corner of the device screen, tap .
3. Tap edit  next to the device name.
4. Tap **Icon** to view the menu.


5. In the slide-up menu, select any one of the following (A) to change the device icon:
- **Take photo** - allows you to click a photo from the mobile camera.
  - **Select from Icon Library** - allows you to select an icon from the app library.
  - **Select from Album** - allows you to select a photo from the mobile gallery.



## Renaming the device


You can rename the device using the Wisser app.


1. On the Home page, select and tap the device you wish to rename.
2. At the top right corner of the device screen, tap .
3. Tap edit  next to the device name.
4. Tap **Name**, enter the new name (A) and then tap **Save**.




## Changing the device location

You can change the device location using the Wisser app.


1. On the Home page, select and tap the device you wish to change the location.
2. At the top right corner of the device screen, tap .


3. Tap edit  next to the device name.
4. Tap **Location**.
5. Select the desired location from the list (A) and then tap **Save**.



## Removing the device

Using the Wiser app, you can remove a device from the device list.  
To remove the device:

1. On the **Home** page, tap **All devices** > **Push-button Dimmer**.
2. Tap  to display more details.
3. Tap **Remove and Factory Reset Device** (A).



**TIP:** Alternatively, you can tap and hold on the **Push-button Dimmer** on the **Home** page to remove the device.

**NOTE:** By removing the device, you will reset the device. If you still have a problem with the reset, then refer to [resetting the device](#), page 11.


## Resetting the device

You can reset the device to factory default manually.  
To reset the device:

1. Short press push button 3 times (< 0.5 s) and then long press the push button once (>10 s).

2. After 10 s, LED starts blinking red then release the push button.  
The LED stops blinking upon successful reset of the device.
3. The Motion Sensor Dimmer restarts and blinks green for a few seconds.

**NOTE:** After reset, the LED turns amber indicating that it is ready for pairing.




## Using the device

The Control Panel allows you to switch the Dimmer On/Off, increase/decrease the brightness and control various settings.

On the **Home** page, tap **All devices** > **Push Button Dimmer** to access the control panel.

On the control panel page, you can see the following:

- The current state of the Dimmer (A)
- Sliding bar to adjust the brightness (B)
- The current brightness percentage (C)
- Schedule, page 14 (D)
- Settings, page 15 (E)




## Switching/Dimming the device manually


You can switch On/Off and increase/decrease the brightness of the dimmer manually. The dimmer will provide power to the load connected to it.

Short press the push-button (< 0,5 s) on the device once to switch On/Off the dimmer.





Long press the push-button ( $> 0,5$  s) on the device to increase/decrease the brightness of the dimmer.




## Switching/Dimming the device using app


Using the Wiser app, you can switch On/Off and increase/decrease the brightness of the device.

### Switch On/Off the device

To switch On/Off the device:

1. On the **Home** page, tap the power button (A) to switch On/Off the Dimmer.




2. Alternatively, you can navigate to the control panel, page 12 of the device and tap  to switch On/Off the Dimmer.

**NOTE:** The control panel shows the current state of the Dimmer.

### Adjusting the brightness of the device

To increase/decrease the brightness of the device:

1. On the **Home** page, tap the **v** (B) and drag the slider to adjust the brightness of the Dimmer.



2. Alternatively, you can navigate to the **control panel**, page 12 of the device and drag the sliding bar up/down to increase/decrease the brightness.

**NOTE:** The control panel shows the current brightness percentage of the Dimmer.


## Creating a schedule

The Dimmer can be controlled and triggered by a schedule. Once the schedule is set, your system will follow the active schedule. You can create or modify the schedules at any time.

To create a schedule:

1. On the **Home** page, tap **All devices > Push-button Dimmer**.
2. Tap **Schedule > Add schedule** to add a schedule.
3. Set the time (A).
4. Tap **Repeat** (B) to select the days you want to set the schedule.
5. Tap **Note** (C), enter the note and tap **Confirm**.
6. Tap the toggle switch (D) to turn On the **Notification** for the schedule. The app will send a notification when the task is executed at the time of schedule.

7. In the Push-button Dimmer section, drag the **sliding bar** (E) to do one of the following:
- **100%** - Turns On the Dimmer with maximum brightness on the scheduled time
  - **Off** - Turns Off the Dimmer on the scheduled time
  - Drag the sliding bar anywhere in between to turn On the Dimmer with a set brightness level on the scheduled time



8. Tap **Save**.

## Dimmer settings

Using The Wiser app, you can manage the Dimmer modes and settings.

To access the dimmer settings:

1. On the **Home** page, tap **All devices > Push Button Dimmer**.
2. On the device control panel page, tap **Settings**.


## Dimming mode

You can change the dimming mode in the app if you have problems with light flickering. This improves the dimming quality.

Tap **Dimming Mode** (A) and select either of the following:

- **Auto** - When any other load is connected to the dimmer (e.g. filament bulb).
- **RL-LED** - When a LED is connected to the dimmer.

**NOTE:** This mode uses 10 % of the nominal load to avoid overheating of the Dimmer, refer to **technical data**, page 27.



## Dimming range

You can restrict the maximum and minimum brightness of the load connected to the device. This is done to avoid flickering and switching off the LED.


Tap **Dimming Range** (B) and do either or both of the following:

– **Min Brightness** - Drag the sliding bar to restrict the minimum brightness.

**TIP:** If you set the minimum brightness to the right most position on this sliding bar, then the load glows at the minimum brightness even if you drag the sliding bar to the lowest value in the [control panel](#), [page 12](#).

– **Max Brightness** - Drag the sliding bar to restrict the maximum brightness.

**TIP:** If you set the maximum brightness to the left most position on this sliding bar, then the load glows at the maximum brightness even if you drag the sliding bar to the highest value in the [control panel](#), [page 12](#).




## Backlight mode

You can select the LED indicator mode for easy identification of the device status.

Tap **Backlight Mode** (C) and select any one of the following:

- **Reverse With Load** - The LED on the Dimmer is On when the device is Off.
- **Consistent With Load** - The LED on the Dimmer is On when the device is On.
- **Always Off** - The LED on the Dimmer is always Off.
- **Always On** - The LED on the Dimmer is always On.




For information on LED color during each modes, refer to [LED indication](#), page 26.

## Toggle mode setting

Using this setting, the device will remember the last state of the device.

Tap **Toggle Mode Setting** (D) and select any one of the following:


- **100%** - The LED glows at maximum brightness every time it is turned On.
- **Last Level (Memory Function)** - The LED glows at the previously set brightness level every time it is turned On.





## Creating a moment

A Moment allows you to group multiple actions that are usually done together. Using the Wiser app, you can create moments based on your needs (such as movie night).

To create a moment:


1. On the **Home** page, tap .
2. Go to **Moment** > **+** to create a moment.
3. Tap **Edit name**, enter the name of the moment (A) and tap **Save**.


**TIP:** You can choose the cover image that represents your moment by tapping .




4. In the **Action** section, tap **Add task** (B) to display the slide-up menu.

5. In the **Add task** menu, you can do either or all of the following actions (C):
- **Run the device** - Select the devices that you want in a moment.
  - **Select Automation** - Select the automation that you want to enable or disable. For more info refer to *Automation*, page 21.
  - **Delay** - Set the delay time.


**NOTE:** You can add one or more actions using .



6. Tap **Run the device > Push-button Dimmer** and select either or both the functions to add in the moment:
- **Dimmer** - turn the Dimmer On/Off (D).
  - **Brightness** - adjust the brightness level (E).



7. Once all the actions are set, tap **Save**.






## Editing a moment

To edit a moment:

1. On the **Moment** tab, locate the moment you want to edit and tap **...**.
2. On the **Edit** page, you can tap each item (such as dimmer, shutter, delay, temperature, etc.) to change the settings.

### TIP:

- You can add one or more actions using .
- To delete an existing action, slide the each item towards left and tap **Delete**.

## Deleting a moment

To delete a moment:


1. On the **Moment** tab, locate the moment that you want to delete and then tap **...**.
2. Tap **Delete** and tap **Ok**.


**NOTE:** After deleting a moment, the device action can no longer be triggered.


## Creating an automation

An automation allows you to group multiple actions that are usually done together, triggered automatically or at scheduled times. By using the Wiser app, you can create automations based on your needs.


To create an automation:

1. On the **Home** page, tap .
2. Go to **Automation** > **+** to create an automation.
3. Tap **Edit name**, enter the name of the automation (A) and tap **Save**.


**TIP:** You can choose the cover image that represents your automation by tapping .




4. Tap **Any condition is met** to select any one of the condition type (B):
- **All conditions are met** - The automation is triggered when all the conditions are met.
  - **Any condition is met** - The automation is triggered when at least one condition is met.




5. Tap **Add Condition** to display the slide-up menu.
6. In the **Add Condition** menu, you can do either or all of the following options (C):
- **When weather changes** - Select the various weather settings.
  - **Schedule** - Set the time and day.
  - **When device status changes** - Select the device and it's function.

Note: You can add one or more conditions using .



7. Tap **When device status changes** > **Push-button Dimmer** and select either or both the functions:


- **Dimmer** - Turn the Dimmer On/Off (D)
- **Brightness** - Adjust the brightness level (E)




8. Tap **Add task** to open the slide-up menu.


9. In the **Add task** menu, you can do either or all of the following options (F):

- **Run the device** - Select the devices that you want to trigger
- **Moment or Automation** - Select the moment which you want to trigger or select the automation that you want to enable or disable
- **Send notification** - Turn On notification for the automation
- **Delay** - Set the delay time

**NOTE:** You can add one or more actions using .



10. Tap on **Effective period** to set the time range for the automation. You can select any one of the following (G):
- **All-day** - 24 hours
  - **Daytime** - From sunrise to sunset
  - **Night** - From sunset to sunrise
  - **Custom** - User defined time period





11. Once all the actions and conditions are set, tap **Save**.  
Once the automation is saved, it is visible on the **Automation** tab. You can tap the toggle switch on the automation to enable it.

## Example of an automation

This demonstration shows you how to create an automation to switch on the light with 50% brightness level when a motion is detected.

**NOTE:** The Dimmer will not be switched Off automatically when the Sensor sends the "Unoccupied" message. To switch off the dimmer when there is no more motion, you must create a new automation.


1. Go to **Automation** > **+** to create an automation.
2. Tap **Edit name**, enter the name of the automation and tap **Save**.  
**TIP:** You can choose the cover image that represents your automation by tapping .
3. Tap **Add Condition** > **When device status changes** > **Motion Sensor**.
4. Tap **Motion State** > **Occupied (A)**.



5. Tap **Add task** > **Run the device** > **Push-button Dimmer**.


6. Tap **Brightness (B)**, adjust the brightness to 50% and tap **Save**.

**TIP:** Setting the brightness level turns on the light the light when the automation is triggered. You need not add a task to turn on the Dimmer separately.



7. Tap **Next**.

8. In the **Automation Settings** page, tap **Save**.



Once the automation is saved, it is visible on the **Automation** tab. You can tap the toggle switch on the automation to enable it.

## Editing an automation

To edit an automation:

1. On the **Automation** tab, locate the automation you want to edit and tap **⋮**.
2. On the **Edit** page, you can tap each item (such as dimmer, shutter, delay, temperature, etc.) to change the settings.

**TIP:**

- You can add one or more actions using **+**.
- To delete an existing condition or action, slide each item towards left and tap **Delete**.

## Deleting an automation



To delete an automation:

1. On the **Automation** tab, locate the automation that you want to delete and then tap **...**.
2. Tap **Delete** and tap **Ok**.



**NOTE:** After deleting an automation, the device action can no longer be triggered.

## LED Indication





### Pairing

| User Action                   | LED Indication  | Status   |
|-------------------------------|---|--|
| Press the push-button 3 times | LED blinks amber per second.<br> | Pairing mode is active for 30 seconds. When pairing is completed, LED glows green for some time before turning Off.<br> |

### Resetting

| User Action   | LED Indication   | Status  |
|---|--|---|
| Press the push-button 3 times and hold it down once for > 10 s. | After 10 s, the LED blinks red.<br> | The device is in reset mode. It is reset to the factory settings after 10 seconds. The device then restarts and the LED blinks green for a few seconds and then stays amber.<br> |

### LED Indicator Mode/Backlight Mode












| Load Status          | ON  | OFF   |
|----------------------|---|---|
| Reverse with load    | No LED  |  |
| Consistent with load |  | No LED  |
| Always Off           | No LED  | No LED  |
| Always On            |  |  |

## Troubleshooting

| Symptom                           | Solution   |
|-----------------------------------|--|
| Dimming up not possible.          | <ul style="list-style-type: none"> <li>• Reduce/increase load.</li> <li>• Allow the Dimmer to cool in case of overheating.</li> <li>• Change the load (if the load is incompatible with the Dimmer).</li> </ul>      |
| Switching On not possible.        | <ul style="list-style-type: none"> <li>• Allow the Dimmer to cool in case of overheating.</li> <li>• Reduce load.</li> <li>• Change load.</li> <li>• Check wiring between the push button and the Dimmer.</li> </ul> |
| Flickering at minimum brightness. | <ul style="list-style-type: none"> <li>• Increase minimum brightness (if flickering still persists, install a 31LCDA load correction device).</li> </ul>   |

| Symptom   | Solution   |
|---|--|
|   | <ul style="list-style-type: none"> <li>Change the load (if the minimum brightness is insufficient).</li> <li>Set to RL LED mode.</li> </ul>                                  |
| Flickering  | <ul style="list-style-type: none"> <li>Change load.</li> <li>Set to RL LED mode.</li> </ul>  |
| Only slight dimming capability  | <ul style="list-style-type: none"> <li>Change dimming range.</li> <li>Set to RL LED mode.</li> <li>Change the load (if the load is incompatible with the Dimmer).</li> </ul> |
| The device is not ready to pair after the device is removed from the app. | Reset to factory default settings, refer to <a href="#">reset the device</a> , page 11.  |

## Technical Data

|  |   |                                |   |
|--|---|--------------------------------|---|
| Nominal voltage                        | AC 230 V ~, 50 Hz   |                                |   |
| Nominal power                          | Load type   | Load name                      | Load value  |
|  |  LED | LED                            | 7–100 VA  RC<br>7–20 VA  RL |
|  |      | Iron core transformer          | 14–150 VA  RL  |
|  |    | Incandescent lamp              | 14–200 W  R   |
|  |    | Halogen lamp                   | 14–150 W  R  |
|  |    | Electronic step-down converter | 14–150 VA  RC  |
| Standby                                | Max 0.4 W   |                                |   |
| Neutral conductor                      | Not required  |                                |   |
| Connecting Terminals                   | Screw terminals for max. 2 x 2.5 mm <sup>2</sup> , 0.5 Nm                             |                                |   |
| Extension unit                         | Single Push-button, unlimited number, max. 50 m                                       |                                |   |
| Fuse protection                        | 16 A circuit breaker  |                                |   |
| Operating frequency                    | 2405 - 2480 MHz   |                                |   |
| Max. radio-frequency power transmitted | < 10 mW   |                                |   |
| Communication protocol                 | Zigbee 3.0 certified  |                                |   |

# Compliance

## Compliance information for Green Premium products

Find and download comprehensive information about Green Premium products, including RoHS compliance and REACH declarations as well as Product Environmental Profile (PEP) and End-of-Life instructions (EOLI).

### General information about Green Premium products

Click the link below to read about Schneider Electric's Green Premium product strategy.

<https://www.schneider-electric.com/en/work/support/green-premium/>

### Find compliance information for a Green Premium product

Click the link below to search for a product's compliance information (RoHS, REACH, PEP and EOLI).

**NOTE:** You will need the product reference number or product range to perform the search.

<https://www.reach.schneider-electric.com/CheckProduct.aspx?cskey=ot7n66yt63o1xblflyfj>

## Trademarks

This guide makes reference to system and brand names that are trademarks of their relevant owners.

- Zigbee® is a registered trademark of the Connectivity Standards Alliance.
- Apple® and App Store® are brand names or registered trademarks of Apple Inc.
- Google Play™ Store and Android™ are brand names or registered trademarks of Google Inc.
- Wi-Fi® is a registered trademark of Wi-Fi Alliance®.
- Wiser™ is a trademark and the property of Schneider Electric, its subsidiaries and affiliated companies.

Other brands and registered trademarks are the property of their respective owners.





Schneider Electric  
35 rue Joseph Monier  
92500 Rueil Malmaison  
France

+ 33 (0) 1 41 29 70 00

[www.se.com](http://www.se.com)

As standards, specifications, and design change from time to time,  
please ask for confirmation of the information given in this publication.

© 2021 – 2024 Schneider Electric. All rights reserved.

DUG\_Unica Push-button dimmer\_WSE-02