

EVlink Home Smart

Device user guide

Information about features and functionality of the devices.

03/2025



Legal Information

The information provided in this document contains general descriptions, technical characteristics and/or recommendations related to products/solutions.

This document is not intended as a substitute for a detailed study or operational and site-specific development or schematic plan. It is not to be used for determining suitability or reliability of the products/solutions for specific user applications. It is the duty of any such user to perform or have any professional expert of its choice (integrator, specifier or the like) perform the appropriate and comprehensive risk analysis, evaluation and testing of the products/solutions with respect to the relevant specific application or use thereof.

The Schneider Electric brand and any trademarks of Schneider Electric SE and its subsidiaries referred to in this document are the property of Schneider Electric SE or its subsidiaries. All other brands may be trademarks of their respective owner.

This document and its content are protected under applicable copyright laws and provided for informative use only. No part of this document may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Schneider Electric does not grant any right or license for commercial use of the document or its content, except for a non-exclusive and personal license to consult it on an "as is" basis.

Schneider Electric reserves the right to make changes or updates with respect to or in the content of this document or the format thereof, at any time without notice.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any errors or omissions in the informational content of this document, as well as any non-intended use or misuse of the content thereof.

Table of Contents

Safety Information.....	4
EVlink Home Smart	5
For your safety	5
About the device.....	6
EVlink Home Anti-tripping System.....	7
Installing EVlink Home Smart	8
eSetup Commissioning	8
eSetup Commissioning- France	9
eSetup Commissioning- International	13
Resetting the PIN using eSetup app	17
Pairing the device to Wiser Home app.....	18
Renaming the device	21
Tariff	21
Charging mode.....	22
Reduce My Bill	23
Anti-Tripping Management	23
Using the device.....	24
Connecting/disconnecting the charger.....	25
Using stop button	26
Managing the cable.....	26
Creating a schedule	27
Automation.....	29
Checking the device history	34
Enabling notifications	34
Removing the device from Wiser system	34
LED indications	35
Troubleshooting	35
Technical data	36
Compliance	39
Product Environmental Data.....	39
Trademarks.....	39

Safety Information

Important Information

Read these instructions carefully and look at the equipment to become familiar with the device before trying to install, operate, service, or maintain it. The following special messages may appear throughout this manual or on the equipment to warn of potential hazards or to call attention to information that clarifies or simplifies a procedure.



The addition of either symbol to a “Danger” or “Warning” safety label indicates that an electrical hazard exists which will result in personal injury if the instructions are not followed.



This is the safety alert symbol. It is used to alert you to potential personal injury hazards. Obey all safety messages that accompany this symbol to avoid possible injury or death.

DANGER

DANGER indicates a hazardous situation which, if not avoided, **will result in** death or serious injury.

Failure to follow these instructions will result in death or serious injury.

WARNING

WARNING indicates a hazardous situation which, if not avoided, **could result in** death or serious injury.

CAUTION

CAUTION indicates a hazardous situation which, if not avoided, **could result in** minor or moderate injury.

NOTICE

NOTICE is used to address practices not related to physical injury.

EVlink Home Smart



EVH4AxxN2
EVH4AxxN400F



EVH4AxxNC

For your safety

⚡⚡ DANGER

HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH

- The equipment must be installed, commissioned, serviced, and maintained only by qualified personnel.
- The charger, the cable and the connector must be regularly checked by to detect any potential damage (visual inspection).
- In case the charger is damaged, it must be immediately turned off and replaced.
- Do not open or modify the charger.

Failure to follow these instructions will result in death or serious injury.

⚠ WARNING**RISK OF INJURY**

- Do not use any extension cable to connect the charger to the electric vehicle.
- Do not connect any other type of loads to the charger (power tools, etc.). Only connect electric vehicles or their charging equipment.
- Do not use brute force to unplug the charging connector from the Electric Vehicle as it is mechanically locked.
- Prevent the connector to be in contact with heat source, dirt or water.
- When using an integrated charger to charge your electric car, please read the vehicle's tips and instructions carefully.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

⚠ CAUTION**RISK OF DAMAGING THE CHARGING STATION**

Never clean the charging point by spraying it with water (Hose for garden watering, high pressure cleaners, etc)

Failure to follow these instructions can result in injury or equipment damage.


About the device

EVlink Home Smart (also referred as EV Charger) provides homeowners with an easy and smart charging experience. This charging station is an electrical appliance that supplies electric energy to charge plug-in electric vehicles for indoor and private outdoor areas. The Wiser app for residential energy management enables easy access to monitor and control the charging experience remotely. Schedule your charging to utilize renewable power charging option. This helps homeowners to optimize consumption, avoid power overruns and reduce the carbon footprint.

The EVlink Home Smart when installed with Anti-Tripping Module, provides you an end-to-end solution and better user experience on power load management. For more information, refer EVlink Home Anti-tripping System, page 7


Operating elements

EVH4AxxN2, EVH4AxxN400F



- A. Cable winding trough
- B. Stop button
- C. LED status indicator
- D. Charging socket

EVH4AxxNC



- A. Cable winding trough
- B. Stop button
- C. Connector unlock button
- D. LED status indicator
- E. Charging connector dock

EVlink Home Anti-tripping System



EVA1HPC1



EVA1HPC3

Overview

Home anti-tripping is a power load management system that continuously adapts the power supplied to charge the car, taking home consumption into account. The power availability is calculated by the anti-tripping system by comparing the utility power limit and the home consumption gathered by a current transformer positioned on the bottom of the main circuit breaker.

NOTE: Anti-tripping module is designed for use with the EVlink Home Smart. Do not use with other electrical devices.

Installing Anti-tripping system

Refer to the installation instruction supplied with this product.

- EVlink Home anti-tripping system 1P+N, EVA1HPC1
- EVlink Home anti-tripping system 3P+N, EVA1HPC3

Installation video: Anti-tripping system installation

Installing EVlink Home Smart

Refer to the installation instruction supplied with this product.

- EVlink Home Smart EVH4AxxN2, EVH4AxxNC
- EVlink Home Smart EVH4AxxN400F

Installation video: EVlink Home Smart installation

eSetup Commissioning

eSetup is a customized, dedicated app for electricians, to make commissioning as simple and easy as possible.

To commission EVlink Home Smart, please download and install eSetup app.

NOTE: This app should only be used by authorized/professional installers.

For Android mobile phones:
Click [here](#) or scan QR code.



For Apple mobile phones:
Click [here](#) or scan QR code.




Once the EVlink Home Smart is installed, follow the steps to commission via eSetup app based on your country.


eSetup Commissioning- France

Once the EVlink Home Smart is installed, follow the steps to commission via eSetup app:

1. Open eSetup app and select **EVlink Home Smart** (A).



2. Power on the EVlink Home Smart to activate the Wi-Fi® access point. The Wi-Fi® access point will remain active for 4 minutes, after power-on.
3. Enable Wi-Fi® on your smartphone and connect to the EVlink Home Smart via Wi-Fi® direct.
4. In eSetup app, tap **Open Settings** (B).




5. Select **EVlink Home Smart - France**.
6. On the screen enter the **New PIN**, confirm the PIN and tap **Save**.
NOTE: The PIN must contain 6 to 16 digits, cannot contain the same digit more than 3 times, or a suit of 6 digits or more.
 New PIN update is successful.
7. On the next page, enter the New PIN and tap **Connect**.
8. On the **firmware** page, if EVlink Home Smart firmware is up to date, tap **Continue** to view **Network Settings**.
NOTE: If a new firmware version is available, tap **Update** and tap **OK** after the update is done.

9. In **Network Settings** page, select the way to connect the EVlink Home Smart to the internet and tap **Save and continue**.


IMPORTANT: If you have a Wiser Hub for remote monitoring and control, make sure that both the EVlink Home Smart and the Hub are connected to the same Wi-Fi® network.

- **Wi-Fi (C):** Tap on **Scan Wi-Fi QR Code** and scan the QR code on your router to connect to Wi-Fi® automatically. Alternatively, you can choose from the list of available networks by tapping **Select a network** or manually enter the Wi-Fi® network name and password.
- **Ethernet (D):** Enter the network details to connect.



10. In **Electrical settings** page, select the power rating of the EVlink to match the electric installation. You can use the **sliding bar (E)** or **-/+** to limit the charging current and tap **Save and continue (F)**.

NOTE: Minimum and maximum charging currents are 10 A and 32 A respectively.




11. In **Device settings** page, you can enable or disable the power meter using the **toggle switch** and then tap **Save and continue**.

NOTE: MID meter is a power meter device that allows you to record the energy consumption of a charging installation. If you enable this option make sure you have connected the power meter to the EVlink Home Smart.

12. In **Energy Management** page, you can enable or disable **TIC Communication** using the toggle switch (G) and then tap **Save and continue** or **Skip this step** as per your need.


NOTE:

- **TIC:** Tele-Information Client with French meter. The TIC device is connected to the switchboard. It will save all data of energy consumption by all devices in the house. This will help to track the energy needed for the EVlink Home Smart. Wiser app manages the Anti-tripping management - delayed charging during peak, off peak hours according to the current information provided by the TIC.
- The EVlink Home Smart is configured in Mode 1. You can enable or disable the communication between the EVlink Home Smart and the TIC device.



13. Tap **Continue** in the **Supervision** page.
14. Once all the device settings are configured, tap **Handover to customer** and share the PIN with the customer.

15. After sharing the PIN, read the instructions and swipe to navigate to next screen. Tap **I understand : restart** (H) to restart the EVlink Home Smart. Please wait for 5 minutes before the EVlink Home Smart connects to the internet router.



- The LED will slowly pulse light green during 5 minutes.
- The EVlink Home Smart shall be restarted according to the applied configuration.

NOTE: In case you need to modify the commissioning parameters, you can reconnect to the EVlink Home Smart during 5 minutes, after restart or power-on.

The LED will turn to solid green 5 minutes after restart confirming that the EVlink Home Smart is successfully connected for remote operation.



NOTE: The LED pulse light green slowly when the EVlink Home Smart is not connected to the internet.

Post-requisite: Use Wiser Home app to monitor and control the EVlink Home Smart.


Refer Pairing the device, page 18 to pair the device with Wiser Home app.

Refer Using the device, page 24 to monitor and control with Wiser Home app.

eSetup Commissioning- International


Once the EVlink Home Smart is installed, follow the steps to commission via eSetup app:

1. Open eSetup app and select **EVlink Home Smart** (A).



2. Power on the EVlink Home Smart charger to activate the Wi-Fi® access point. The Wi-Fi® access point will remain active for 4 minutes, after power On.
3. Enable Wi-Fi on your smartphone and connect to the EVlink Home Smart via Wi-Fi direct.

4. In eSetup app, tap **Open Settings** (B).



5. Select **EVlink Home Smart - International**

6. On the screen enter the **New PIN**, confirm the PIN and tap **Save**.

NOTE: The PIN must contain 6 to 16 digits, cannot contain the same digit more than 3 times, or a suit of 6 digits or more.

New PIN update is successful.

7. On the next page, enter the New PIN and tap **Connect**.


8. On the firmware page, if EVlink Home Smart firmware is up to date, tap **Continue** to view **Network Settings**.

NOTE: If a new firmware version is available, tap **Update** and tap **OK** after the update is done.

9. In **Network Settings** page, select the way to connect the EVlink Home Smart to the internet and tap **Save and continue**.


IMPORTANT: If you have a Wiser Hub for remote monitoring and control, make sure that both the EVlink Home Smart and the Hub are connected to the same Wi-Fi® network.

- **Wi-Fi (C):** Tap on **Scan Wi-Fi QR Code** and scan the QR code on your router to connect to Wi-Fi automatically. Alternatively, you can choose from the list of available networks by tapping **Select a network** or manually enter the Wi-Fi network name and password.
- **Ethernet (D):** Enter the network details to connect (use RJ45 cable type).



10. In **Electrical settings** page, select the power rating of the EVlink to match the electric installation. You can use the **sliding bar** (E) or **–/+** to limit the charging current and tap **Save and continue** (F).

NOTE: Minimum and maximum charging currents are 10 A and 32 A respectively.




11. In **Device settings** page, you can enable or disable the power meter using the **toggle switch** and then tap **Save and continue**.

NOTE: If you enable this option make sure you have connected the power meter to the EVlink Home Smart.

12. Tap **Continue** in the **Supervision** page.
13. Once all the device settings are configured, tap **Handover to customer** and share the PIN with the customer.


14. After sharing the PIN, read the instructions and swipe to navigate to next screen. Tap **I understand : restart** (G) to restart the EVlink Home Smart. Please wait for 5 minutes before EVlink Home Smart connects to the internet router.



- The LED will slowly pulse light green during 5 minutes.
- EVlink Home Smart shall be restarted according to the applied configuration.

NOTE: In case you need to modify the commissioning parameters, you can reconnect to the charging station during the 5 minutes, after restart or power-on.

The LED will turn to solid green 5 minutes after restart confirming that EVlink Home Smart is successfully connected for remote operation.



NOTE: The LED pulse light green slowly when the EVlink Home Smart is not connected to the internet.

Post-requisite: Use Wiser Home app to monitor and control the EVlink Home Smart.


Refer Pairing the device, page 18 to pair the device with Wiser Home app.

Refer Using the device, page 24 to monitor and control with Wiser Home app.

Resetting the PIN using eSetup app

If eSetup PIN code is lost, you can reset the PIN code to default value using the eSetup app.

1. Power on the EVlink Home Smart to activate the EVlink Home Smart Wi-Fi® direct.
The Wi-Fi® direct will remain active for 4 minutes after power on.
2. Open eSetup app and select **EVlink Home Smart**, and then tap **Open Settings**.
3. Select **EVlink Home Smart - International** or **EVlink Home Smart - France** based on where the EVlink Home Smart is installed.
4. On the screen enter the **New PIN**, confirm the PIN and tap **Save**.
5. Tap **Reset PIN** (A) and select **Confirm** (B).



6. Press the **Stop** button within 3 minutes, 30 seconds.

NOTE: Unlock the Stop Button by rotating it 90° clockwise.



- After 10 seconds, enter the **New PIN**, confirm the PIN and tap **Save**.

NOTE: The PIN must contain 6 to 16 digits, cannot contain the same digit more than 3 times, or a suit of 6 digits or more.






New PIN update is successful.

Pairing the device to Wiser Home app

IMPORTANT: Make sure that the EVlink Home Smart has been configured by an electrician.

To pair the device:

- On the **Home** page, tap .
- Tap **Devices** >  > **Energy**.
- Select **EVlink Home Smart**.
- On **EVlink Home Smart Setup** page, tap **Next**.




5. Tap **Open camera** to scan QR code on your EVlink terminal.



A notification window will prompt you to authorize Wiser Home to access your camera.

6. Tap **OK**.



7. Point the camera and scan the QR code near the charging socket/connector dock.





You need to wait for up to 5 minutes for the **EVlink Home Smart** to join the setup.

8. If you wish to name the EVlink Home Smart, tap  and enter a name.

NOTE: By default, the name will appear as **EVlink Home Smart**.

9. Tap **Next** and then tap **Finish**.




On successful pairing, the EVlink Home Smart will appear on the app's **Control** page.

NOTE: If you only have an EV Charger in the Wiser System, the **Control** page will not be visible. All functions will be accessible through the **Home** page.

Renaming the device

Using the Wiser Home app, you can rename your device for easy identification.

1. On the **Control** tab, tap **All > EV Charger > Device settings**.
2. Tap  next device name and then enter a new name.

The settings will be saved automatically.

Tariff

You can set tariff in the Wiser Home app to access your energy cost and billing data.

To accurately deliver real-time information on energy consumption, it is essential to include the relevant tariff information. The cost associated with energy consumption is determined by your specific contract type. The different contracts will have varying rates, which can affect how much you pay for the energy you use. By providing the tariff details, we can make sure that the energy consumption data reflects the most accurate costs, helping you better understand your energy usage and manage your expenses effectively.

The cost of energy consumption is based on below contract type:

- Flat rate
- Peak/Off-Peak Hours rate
- No contract

For more information on **Setting Tariff** refer to the respective [System User Guide](#).

Charging mode


Using the Wiser Home app, you can manage the mode of charging.

1. On the **Control tab**, tap **All devices > EV Charger**.
2. On the device control panel page, tap **Charging Mode**.
3. On the **EV Charging Mode** menu, select any one of the following options:
 - A. **Charge Now:** charging will start as soon as the cable is plugged in to Electric vehicles (EV).
 - B. **Reduce My Bill:** your electric vehicle will automatically start charging at the next cost effective time period based on the tariff to reduce your total cost of charging.

IMPORTANT: This feature is applicable only when there are suitable tariffs created. Refer to Reduce My Bill and Tariff plan configuration.

- C. **Customized Schedule:** create your own schedule to charge your electric vehicle.

Refer to [Creating a schedule](#), page 27.



NOTE: For more information on Reduce My Bill and Setting Tariff refer to the respective System User Guide.

NOTE: You can change the charging mode at any time.

Reduce My Bill

Using the Wiser Home app, you can view how the devices are controlled and scheduled for usage.

The Reduce My Bill feature automatically schedules your high-consuming devices to run during the cheapest electricity rates, helping to lower your energy bill. By enrolling devices like EV chargers or resistive water boilers, this feature shifts loads to low-tariff periods. It works with variable tariffs, such as peak/off-peak rates, and requires users to answer routine questions.

For more information on **Reduce My Bill** refer to the respective System User Guide.

Anti-Tripping Management

The Anti-Tripping Management prevents the circuit breaker from tripping by switching off the load (e.g. Water Heater, EV Socket) or reducing the power of the load.

The Power Consumption Management (PCM) system is an advanced algorithm designed to prevent global overconsumption. It achieves this by reducing setpoints and shutting down specific loads, ensuring that overall energy consumption stays within a predefined limit. With the integration of Wiser Home, users gain enhanced control over the loads monitored by the PCM. You can enroll up to eight loads at a time, which helps maintain the total consumption of the system below the established limit. This limit is determined by your contract specifications, so it's important to refer to the [Setting Tariff](#) section for information on peak and off-peak rates. Eligible devices will be automatically incorporated into the Anti-Tripping Management system, further optimizing energy usage and enhancing the overall efficiency of your home energy management.

For more information on **Anti-Tripping Management** refer to the respective System User Guide.


Using the device

The Control Panel allows you to start and stop charging and monitor the power consumption.

On the **Control** page, tap **EV Charger** to access the control panel.


On the control panel page, you can see the following:

- Total cost of charging session (A).
- Total time of charging in the session (B).
- Total energy consumption in the session (C).
- Control button (Start charging/Stop charging, Pause/Resume) (D).
- Charging Mode, page 22 (E).
- Device settings (F) - You can rename the device or remove the device from the Wiser system. Refer to [Renaming the device](#), page 21 and [Removing the device](#), page 34.
- History, page 34 (G).



Similarly you can control and check the current status of EV from **Control** page.

- Control button (H).
- Current state of the device (I).



TIP: You can also start and stop charging when you add the device to your Favorite list. For more details about Favorites, refer to the respective System User Guide.

NOTE:

- If you only have an EV Charger in the Wiser System, the **Control** page will not be visible. All functions will be accessible through the **Home** page.
- Electric vehicles (EV) can't be charged immediately after they have stopped. Reconnect the plug to start charging. Refer [Connecting/disconnecting the charger](#), page 25.

Connecting/disconnecting the charger

Connecting

1. Plug in the charging cable connector into the EV Charger.
2. Plug in the charging cable connector into the electric vehicle's inlet.
3. The EV Charger's LED indicator will change from constant green to pulsing blue.


NOTE: For information on LED color, refer to [LED indication](#), page 35.

Disconnecting

1. Stop charging the vehicle with Wiser Home app to unlock the charging cable from vehicle socket.
2. Unplug the EV Charger's connector from the electric vehicle's inlet.
3. Wind the charging cable around the EV Charger winding trough.

Using stop button


EVlink Home Smart has a stop button to cut off electricity between the charger and the car if the connection cannot be shut down normally.



NOTE: Stop button can also be used to reset the PIN by rotating it 90° clockwise. Refer resetting the PIN, page 17.

Managing the cable

- Ensure that the charging connector and charging cable are securely stored between charging sessions.
- Wrap the charging cable around the EVlink Home Smart's cable trough.
- If EVlink Home Smart is installed indoors, protect the connector by covering it with the dust cap.
- If EVlink Home Smart is installed outdoors, store the connector by plugging it into the socket of the EVlink Home Smart.




Creating a schedule

The EV charging can be controlled and triggered by a schedule. Once the schedule is set, your system will follow the active schedule. You can create or modify the schedules at any time.

1. On the **Control** tab, tap **All > EV Charger**.

2. Tap **Charging Mode**.

NOTE: If you have EV Charger installed with Wiser Hub you can also navigate the following path to create schedules:


- On the **Home** screen, tap .
- Tap **Schedules > EV schedule**. Proceed with step 3.

3. On the **EV Charging Mode** page, select **Customized Schedule**.


NOTE: The EV Charger will have a default schedule pre set to the user. You can edit the schedule as required.

IMPORTANT: It is required to set an **On** and **Off** state for a schedule.



4. Select days (A).


5. Tap  (B) to edit the schedule.

6. Select a state (On/Off) (C), time period (D) and tap **Set**.



TIP:

- You can add multiple schedules based on your requirement. Select days (A), tap  (E), set on/off state and time.
- You can copy the existing schedule to the days of your choice. Tap  (F), select the days and tap **Copy**.



- When the schedule begins, you can see the **until time** on the control tab under the device name.




Automation

Automation is applicable only for users with **EV Charger** and **Wiser hub** installed together. An automation allows you to group multiple actions that are usually done together, triggered automatically or at scheduled times. By using the Wiser Home app, you can create automations based on your needs.


Creating an automation


The following is an example of creating an automation to start the EV Charger when you are away.


NOTE: EV Charger can only act as an action.


1. On the **Home** page, tap .
2. Go to **Automation** and then tap  to create an automation.
3. Tap  and choose an icon that best represents your automation.
4. Enter a name of the automation (A) and select any of the following conditions to meet (B).
 - **All conditions:** All conditions must be met to trigger an automation
 - **Any condition:** Any one of the condition must be met to trigger an automation.
5. Tap **Add conditions** (C) and select any of the following (D):
 - **Device status change** (Select the device)
 - **Away Mode** (Enable or Disable)

NOTE: Maximum 10 conditions can be added.



6. Select **Enabled mode away (E)**.


NOTE: To remove an added condition, swipe left and tap .





7. To add an action, tap **Then > Add an action** and select any of the following. In this case, **Control a device** (F).

NOTE: Maximum 10 actions can be added.


- **Control a device:** Select a device that you want to trigger.
- **Send notification:** Turn on the notification for the automation.
- **Activate a moment:** Select the moment that you want to trigger.
- **Wait:** This option allows you to add a delay in an automation sequence. You can set the wait time in increments of 1 hour and 1 minute, up to a maximum of 24 hours. This feature is useful for delaying actions within an automation.



8. Select **EV Charger** (G) and then select an action (H) to assign.









9. Tap **Save** (I).



The saved Automation is displayed on the **Automation** page. Tap the toggle switch on the **Automation** page to enable/disable the Automation.


Editing an automation


- On the **Home** screen, tap **Automations** .
- Go to **Automation**, tap the automation you want to edit.
- On the **Edit automation** page, you can perform following changes:
 - Change the icon .
 - Rename the automation.
 - Tap each condition to change the settings.
 - To remove a condition, slide the condition towards left and then tap  (A) to delete it.
 - Tap  **Add conditions** (B) to add new condition.
 - To change the order of actions, tap the **Then** option, and hold an action then drag and drop to the desired position.



- Tap **Save** to save the changes.

Deleting an automation

1. On the **Home** screen, tap **Automations** .
2. Go to **Automation**, tap the automation you want to delete.
3. On the **Edit automation** page, tap **Delete automation** (A) and read the confirmation message and then tap **OK** (B).



Checking the device history

Using the Wiser Home app, you can monitor the cost and power consumption of the EV Charger by accessing the history.

1. On the **Control** tab, tap **All > EV Charger**.
2. On the device control panel page, tap **History**.
3. In the **History** page, you can see the total power consumption per charging cycle and total charging cost.


You can tap **Load More** to view the records of the past 30 days.

History	
December - 3 Charges	
Today 19:00 1h 10min	3.9 kWh ▾
Yesterday 06:50 6h	10.8 kWh ▾
Yesterday 18:01 52 min	1.2 kWh ▴
Plugged In	18:01 am
Stopped	18:53 am
Total Charging Cost	£1.78
5/12/2021 18:01 52 min	1.2 kWh ▾
November - 24 Charges	
13/10/2021 18:01 52 min	1.2 kWh ▾
Load More	

IMPORTANT: If you have installed both PowerTag and EV Charger, you can monitor the powerflow and energy consumption in the **Energy** tab. For more information, refer to [Live](#).

Enabling notifications

Using Wiser Home app, you can enable notifications to view the charging status.

1. On the **Home** screen, tap .
2. Tap **Account > Notifications**.
3. Enable the **EV Charger** toggle switch.


Removing the device from Wiser system

Using the Wiser Home app, you can remove a device from the device list.

1. On the **Home** page, tap **All > EVlink Home Smart > Device settings**.

NOTE: Tap **Help and support** to view the website where you can find answers to your queries.

2. Tap **Remove from System** for confirmation window to be prompted.










3. Tap **OK** to confirm.

The app will direct the user to the **Home** page. All the app related data will be deleted.


LED indications

Charger status

LED color	LED behaviour	Charger status
	Solid	Ready to charge / Connected to internet
	Pulsing (1 s)	Firmware upgrade
	Breathing (5 s)	Not connected / Connection tentative ongoing
	Solid	Charge ended
	Breathing (5 s)	Charging
	Pulsing (1 s)	Charge suspended
	Solid	Stop or error, please refer to troubleshooting, page 35.

Troubleshooting

Symptom	Possible causes and solutions
Connector plugged into electric vehicle but not charging.	<ul style="list-style-type: none"> Verify that the connector is inserted properly by unplugging and plugging it back into the electric vehicle's socket. Verify the charging sequence by following the procedure described in connecting the charger, page 25.

Charger's LED light green slow pulsing (EVlink Home Smart only)	<ul style="list-style-type: none"> • Reboot the EVlink Home Smart and wait 10 s before to energize it. • EVlink Home Smart is not connected to the cloud If using Wi-Fi: <ul style="list-style-type: none"> ◦ Verify that you connect EVlink Home Smart to a 2.4 GHz Wi-Fi with WPA2 password ◦ Verify that the SSID and password are correct. ◦ In case the Wi-Fi signal is too weak: connect the charger with Ethernet cable, or add a Wi-Fi range extender.
Charger's LED illuminated red.	<ul style="list-style-type: none"> • Verify that the stop button isn't locked, by rotating it 90° clockwise. • If not, switch off the power supply of the charger. • Unplug the connector from the electric vehicle. • Switch on the power supply, wait for the charger to become ready (LED glows green), before reconnecting the connector to the electric vehicle. • Check the power supply is securely wired to the charger's PE (Protective Earth) terminal.
Charger's LED off.	<ul style="list-style-type: none"> • No power supply as charger might be damaged. • Switch off the power supply to the charger. • Please contact Schneider Electric's Customer Care Centre.
Charger's LED red blinking (*Applicable only to France.)	<ul style="list-style-type: none"> • Verify that the TIC cable is connected correctly or not for EVlink Home Smart with TIC function.
Device not removed from the system	<ul style="list-style-type: none"> • Hub disconnected from the network. (Applicable only for users with EVlink Home Smart and Wiser hub installed together) • Charger unavailable. • Device connected to another home network. • Try setting up the device again. • If still the error persists, contact customer support. • Tap Help and support in Device Details page.
Device not paired with the Hub	<ul style="list-style-type: none"> • Hub disconnected from the network. (Applicable only for users with EVlink Home Smart and Wiser hub installed together) • Charger unavailable. • Device connected to another home network. • When you enroll another device, the hub will block from re-enrolling it (as user can only register one device). • Contact customer support - tap Help and support in Device Details page.
 We are unable to implement your schedule and are working on fixing it as soon as possible. displayed in the Reduce My Bill page.	<p>Internet or technical issue.</p> <p>Wait for sometime until the schedule is available.</p>

Technical data

EVlink Home Smart

Range	EVlink Home
Product name	EVlink Home Smart
Product type	AC charging station
Pole description	3P + N for power circuit 1P + N for power circuit
Mounting mode	Wall-mounted
(Us) rated supply voltage	400 Vac 50 Hz + / - 10 % - 3 phase 230 Vac 50 Hz + / - 10 % - 1 phase
Nominal output power	11 kW 16 A 7.4 kW 32 A 3.7 kW 16 A
Maximum supply current	32 A

EVlink Home Smart (Continued)

	16 A
Maximum power	11 kW (3PH) 7.4 kW (1PH) 3.7 kW (1PH)
Access control system	No RFID and no lock
Circuit protection	Need to have a dedicated MCB (Miniature Circuit Breaker)
Under voltage protection	Connected to an IMNX is recommended
Insulation disturbance protection	Need to have a RCD (Residual Current Device) type A and 3,7 kW 16 A
Socket number	1
Socket-outlet type	Front face T2 Socket Front face T2S socket 5 m attached cable
Earthing system	TT TN-S Compatible IT with additional isolation transformer on the power supply.
Input type	Possibility to add an Anti-tripping Module EVA1HPC1 (1PH) or EVA1HPC3 (3PH)
Control type	1 red button, function: Stop No action required to start the charge
Local signaling	1 multi-color LED, function: status indication
Communication	Protocol OCPP 1.6 J for connectivity to Wiser app Wi-Fi® connection or Ethernet connection to Home Internet Box
Smart phone application	Free access to WISER (Schneider Electric Home Smart Phone application to manage home devices and energy)
Remote features	Scheduling Remote start/stop Monitoring and history
Metering	In-built microprogrammed Control Unit for measurement: accuracy 1% Modbus connection for external Schneider Electric MID power meter (A9MEM3155/A9MEM2155)
Standards	EN 61851-1 Ed3.0 EN 61000-6-1 EN 61000-6-3 IEC 61851-21-2
Product certifications	CE UKCA
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30 to 50 °C
Ambient air temperature for storage	-40 to 85 °C
Relative humidity	5 to 95%
Height	409 mm
Width	282 mm

EVlink Home Smart (Continued)

Depth	148 mm
Net weight	15,6 kg (3PH) 4.5 kg (1PH)
Color	White Black

EVlink Home Anti-tripping System

Power supply	220/230 V ($\pm 10\%$)
Frequency	50/60 Hz
Rated power	4 W
Overvoltage category	III
Pollution degree	2
Insulation degree	reinforced insulation
Sampling current range	AC 1 to 100 A / period is 1 second
Possible max. current value settings	16 A, 20 A, 25 A, 32 A, 40 A, 50 A
Communication	Power Line Carrier with EVlink Home charging station
Warranty	24 months for the entire EVlink Home range
Nominal temperature	-30 °C to +50 °C
Dimensions (L × W × H)	70.4 × 93.2 × 68.8 mm
Mounting type	Top-hat rail mounting
Weight	196 g
Certification	EN 61010-1-2010, EN 61326-1-2013

Compliance

Product Environmental Data

Find and download comprehensive environmental data about your products, including RoHS compliance and REACH declarations as well as Product Environmental Profile (PEP), End-of-Life instructions (EOLi) and much more.

<https://www.se.com/myschneider>



General information about Schneider Environmental Data Program

Click the link below to read about Schneider Electric's Environmental Data Program.

<https://www.se.com/ww/en/about-us/sustainability/environmental-data-program/>



Trademarks

This guide makes reference to system and brand names that are trademarks of their relevant owners.

- Zigbee® is a registered trademark of the Connectivity Standards Alliance.
- Apple® and App Store® are brand names or registered trademarks of Apple Inc.
- Google Play™ Store and Android™ are brand names or registered trademarks of Google Inc.
- Wi-Fi® is a registered trademark of Wi-Fi Alliance®.
- Wiser™ is a trademark and the property of Schneider Electric, its subsidiaries and affiliated companies.

Other brands and registered trademarks are the property of their respective owners.

Schneider Electric
35 rue Joseph Monier
92500 Rueil Malmaison
France

+ 33 (0) 1 41 29 70 00

www.se.com

As standards, specifications, and design change from time to time, please ask for confirmation of the information given in this publication.

© 2023 – 2025 Schneider Electric. All rights reserved.

DUG_EVlink_WH-05