

Smart Equipment

0614DB1801

Data Bulletin

Data Acquisition with PowerPacT™ and MasterPacT™ Devices.

0614DB1801

04/2025



Smart Equipment

Technical guide
Data acquisition
with PowerPacT, MasterPacT Devices

Measure

Connect

Protect

A large industrial power distribution unit (PDU) is shown in the foreground. To its right, a computer monitor displays a complex software interface with multiple graphs and data tables. A smartphone below the monitor shows a similar but smaller version of the same interface. Three colored callout boxes point from the text on the left to the PDU: an orange box points to the top section of the PDU, a green box points to the middle section, and a blue box points to the bottom section. The background features a blurred image of a man in a blue shirt looking down at a computer screen.

Legal Information

The information provided in this document contains general descriptions, technical characteristics and/or recommendations related to products/solutions.

This document is not intended as a substitute for a detailed study or operational and site-specific development or schematic plan. It is not to be used for determining suitability or reliability of the products/solutions for specific user applications. It is the duty of any such user to perform or have any professional expert of its choice (integrator, specifier or the like) perform the appropriate and comprehensive risk analysis, evaluation and testing of the products/solutions with respect to the relevant specific application or use thereof.

The Schneider Electric brand and any trademarks of Schneider Electric SE and its subsidiaries referred to in this document are the property of Schneider Electric SE or its subsidiaries. All other brands may be trademarks of their respective owner.

This document and its content are protected under applicable copyright laws and provided for informative use only. No part of this document may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Schneider Electric does not grant any right or license for commercial use of the document or its content, except for a non-exclusive and personal license to consult it on an "as is" basis.

Schneider Electric reserves the right to make changes or updates with respect to or in the content of this document or the format thereof, at any time without notice.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any errors or omissions in the informational content of this document, as well as any non-intended use or misuse of the content thereof.

Schneider Electric, EverLink, Green Premium, I-Line, MasterPacT, MicroLogic, PowerPacT and Square D are trademarks and the property of Schneider Electric SE, its subsidiaries and affiliated companies. All other trademarks are the property of their respective owners.

Table of Contents

Energy Management using Smart Equipment	5
Five Types of Information.....	6
Two Ways to Access Information	7
Communication Accessory Abbreviations	7
Data Acquisition.....	8
PowerPacT H, J, and L Circuit Breakers.....	8
Metering, Measurement, and Quality.....	8
Metering, Measurement, Quality, and Availability	11
Metering, Measurement, Quality, Availability, and Control	15
Drawout Device (Base or Cradle).....	20
PowerPacT P/R and MasterPacT NT/NW Circuit Breakers	22
Metering, Measurement, Quality and Availability, Fixed Device	22
Metering, Measurement, Quality, Availability, and Control	25
MasterPacT NT/NW Circuit Breakers.....	27
Metering, Measurement, Quality, and Availability	27
Metering, Measurement, Quality, Availability, and Control	30
MasterPacT MTZ Circuit Breakers	33
Metering, Measurement, Quality, Availability, and Control	33
Metering, Measurement, Quality, and Availability for MasterPacT MTZ	34
Multi-Product Architecture Examples	35
Hybrid Communication - Ethernet and Modbus.....	35
24 Vdc Power Supply.....	36
24 Vdc Power Supply and Unit Consumption.....	37
Calculation Examples	38

Energy Management using Smart Equipment

Schneider Electric's exclusive Smart Equipment can be fully directed to company IT networks to help improve energy performance.

This user guide provides basic information on the Enerlin'X system and how it can be used to design, build, and configure Smart Equipment.

The guide can help determine how to equip circuit breakers and other protective devices in the PowerPacT and MasterPacT ranges, depending on the information required from each of them. This guide is a supplement to the other Smart Equipment design and construction documents.

For additional information about Enerlin'X, see catalog 0614CT1802, Enerlin'X Digital Solutions for Smart Systems Catalog.

For additional information about ULP, see user guide DOCA0093EN, ULP (Universal Logic Plug) System User Guide.

For additional information about Modbus, see user guide 0611IB1302, PowerPacT H-, J-, and L-Frame Circuit Breakers — Modbus Communication Guide.



Enerlin'X Catalog



0614C-T1802



ULP System User Guide



DO-CA0093E-N



0611-B1302

Modbus Communication Guide



1 Measure

Embedded and stand-alone metering & control capabilities

2 Connect

- > Integrated communication interfaces
- > Ready to connect to energy management platforms

3 Protect

- > Data-driven energy efficiency actions
- > Real time monitoring and control
- > Access to energy and site information through on-line services



Five Types of Information

Below are definitions of the five types of information available through the Enerlin'X system. First, select the relevant information types for your application, then consult the Data Acquisition section of this document for the equipment options.



Metering

Indicates the electricity consumption.



Measurement

Provides a real-time indication of electricity consumption and can track its rise or fall.

- MicroLogic A trip units provide adjustable protection and have a built-in ammeter.
- MicroLogic E trip units provide MicroLogic A functions plus energy measurements.
- MicroLogic P trip units provide MicroLogic E functions plus basic power monitoring and metering functions.
- MicroLogic H trip units provide MicroLogic P functions plus enhanced power monitoring, and power quality measurements.



Quality

For the same electricity consumption, the installation capacity may be over-used or under-used.



Availability

Information about the state of the device.



Controls

Control signals switch the loads on or off.

Two Ways to Access Information



Directly via the front panel



Remotely via IT network

Communication Accessory Abbreviations


- **BCM:** Breaker Communication Module
- **BSCM:** Breaker Status and Control Module
- **FDM:** Front Display Module
- **IFE:** Interface Ethernet Module
- **IFM:** Interface Modbus SL Module
- **I/O:** Input/Output Module


Data Acquisition

PowerPacT H, J, and L Circuit Breakers


Metering, Measurement, and Quality

Front Display Panel




Remote View

Front Panel Display and Remote View




Metering, Measurement, Quality, and Availability


Front Panel Display




Remote View using ULP




Front Panel Display and Remote View using ULP




Remote View using Modbus SL

Front Panel Display and Remote View using Modbus SL




Metering, Measurement, Quality, Availability, and Control


Front Panel Display




Remote Control using ULP




Front Panel Display and Remote Control using ULP





Remote Control using Modbus SL





Front Panel Display and Remote Control using Modbus SL

Drawout Device (Base or Cradle)

List of References







PowerPacT P/R and MasterPacT NT/NW Circuit Breakers


Metering, Measurement, Quality and Availability, Fixed Device

Fixed Device, Front Panel Display




Fixed Device, Remote View

Fixed Device, Front Panel Display, and Remote View




Metering, Measurement, Quality, Availability, and Control


Fixed Device, Front Panel Display



Fixed Device, Remote View




Fixed Device, Front Panel Display, and Remote View




MasterPacT NT/NW Circuit Breakers


Metering, Measurement, Quality, and Availability

Drawout Device, Front Panel Display




Drawout Device, Remote View

Drawout Device, Front Panel Display, and Remote View




Metering, Measurement, Quality, Availability, and Control


Drawout Device, Front Panel Display



Drawout Device, Remote View




Drawout Device, Front Panel Display, and Remote View




MasterPacT MTZ Circuit Breakers

Metering, Measurement, Quality, Availability, and Control

Smart device-Based View




Remote View



ULP Port Modules		
	MasterPacT MTZ1 fixed circuit breaker	LV850063SP
	MasterPacT MTZ2/MTZ3 fixed circuit breaker	LV850061SP
	MasterPacT MTZ1 drawout circuit breaker	LV850064SP
	MasterPacT MTZ2/MTZ3 drawout circuit breaker	LV850062SP


Metering, Measurement, Quality, and Availability for MasterPacT MTZ

Smart device-Based View and Remote View



Multi-Product Architecture Examples


Hybrid Communication - Ethernet and Modbus




24 Vdc Power Supply

24 Vdc Power Supply and Unit Consumption

PowerPacT H, J, L
with IFM interface and display



PowerPacT P, R and MasterPacT NT/NW
with IFM interface and display




Product	Consumption
FDM121 display	21 mA
IFM interface	21 mA
BSCM module	9 mA
MicroLogic circuit breaker control unit	30 mA
Total	81 mA

Product	Consumption
FDM121 display	21 mA
IFM interface	21 mA
BCM ULP module	40 mA
MicroLogic circuit breaker control unit	100 mA
Total	182 mA

Multi-Product Calculation Example


MasterPacT NT/NW circuit breaker with IFE Ethernet interface, Five PowerPacT H/J/L devices with RS485 IFM interfaces, and one FDM128 front display module



Product	Consumption	Qty
FDM128 display	285 mA	1
IFE Ethernet interface	120 mA	1
BCM ULP module	40 mA	1
MicroLogic PowerPacT P, R	100 mA	1
IFM interface	21 mA	5
BSCM module	9 mA	5
MicroLogic PowerPacT H/J/L	30 mA	5
Total	845 mA	

24 Vdc Power Supply and Unit Consumption


PowerPacT P/R, MasterPacT NT/NW




BCM ULP module
40 mA

MicroLogic P/H
100 mA


Shared accessories




FDM128 display
285 mA




FDM121 display
21 mA



I/O module
165 mA




IFE Ethernet interface
120 mA



IFM Modbus interface
21 mA

PowerPacT H/J/L



BSCM module
9 mA

MicroLogic
30 mA


24 Vdc Power Supply Unit	AD Range	Phaseo Range		
Nominal Current	1 A	3 A	5 A	10 A
Primary Surge Category	IV		II	
24/30 Vdc input	685823		—	
48/60 Vdc input	685824		—	
100/125 Vdc input	685825		—	
110/130 Vac input	685826	ABL8RP-S24030	ABL8RP-S24050	ABL8RP-S24100
200/240 Vac input	685827			

NOTE: Example of other compliant power supplies: Phoenix Contact TRIO POWER power supply unit, TRIO-PS-2G/1AC/24DC/10/B+D (part number 2903145).


Calculation Examples

Single Product Calculation Examples

PowerPacT H, J, L
with IFM interface and display



PowerPacT P, R and MasterPacT NT/NW
with IFM interface and display




Product	Consumption
FDM121 display	21 mA
IFM interface	21 mA
BSCM module	9 mA
MicroLogic circuit breaker control unit	30 mA
Total	81 mA

Product	Consumption
FDM121 display	21 mA
IFM interface	21 mA
BCM ULP module	40 mA
MicroLogic circuit breaker control unit	100 mA
Total	182 mA

Multi-Product Calculation Example

MasterPacT NT/NW circuit breaker with IFE Ethernet interface, Five PowerPacT H/J/L devices with RS485 IFM interfaces, and one FDM128 front display module



Product	Consumption	Qty
FDM128 display	285 mA	1
IFE Ethernet interface	120 mA	1
BCM ULP module	40 mA	1
MicroLogic PowerPacT P, R	100 mA	1
IFM interface	21 mA	5
BSCM module	9 mA	5
MicroLogic PowerPacT H/J/L	30 mA	5
Total	845 mA	

Schneider Electric USA, Inc.
800 Federal Street
Andover, MA 01810 USA

888-778-2733

www.schneider-electric.us

As standards, specifications, and design change from time to time, please ask for confirmation of the information given in this publication.

© 2019 – 2025 Schneider Electric. All rights reserved.

0614DB1801